

140W USB-C Wall Charger, USB-IF Certified, Single USB-C, PD 3.1 Portable GaN Charging, Power Adapter for MacBook M3 Pro/Max, Dell XPS/Inspiron/Precision

Produkt-ID: 1014GCN-WALL-CHARGER



This USB-IF Certified 140W USB-C GaN Charger delivers a versatile, high-power charging solution for USB-C devices, supporting up to 140W with PD 3.1. The package includes a 6 ft (1.8 m) USB-C cable, so you have everything needed for immediate, reliable charging.

The USB-IF Certified Power Adapter and included USB-IF Certified USB Type-C cable provide safe and reliable charging solutions. Supporting high-performance USB Power Delivery (PD) 3.1 with Extended Power Range (EPR), this adapter can charge demanding 140W devices, including the MacBook M3 Pro/Max. Its robust design accommodates current laptops like the MacBook Air, Dell XPS, iPad Pro, iPhone, Samsung smartphones, and Google Pixel, while also ensuring future-proof compatibility with next-generation devices.

This USB Wall Charger is engineered for optimal cooling, providing a safer, more reliable charging experience. Balancing compact size with powerful functionality, it features a foldable North American power plug (NEMA 1-15P) for easy storage and delivers fast, efficient charging while maintaining long-lasting performance. At just 10.5 oz (299 g), this travel-friendly adapter combines robust capabilities with easy portability, making it an ideal companion on the go.

Safety and efficiency are paramount with the 140W USB GaN Charger. It is TUV Safety Listed (IEC 62368-1) and FCC/ICES EMC certified, providing protection against over-voltage, current, and temperature. The Active Power Factor Correction (PF > 0.99) enhances efficiency and ensures cool operation. Additionally, it meets DOE Level VI standards, guaranteeing energy efficiency and reliable performance.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Ideal for travel with a light weight design and port variation eliminating the need to carry multiple chargers for different devices
- Power laptops and other USB devices in at the office or home office

Merkmale

- **140W USB GaN CHARGER:** USB wall charger with 1x USB-C (140W max, PD 3.1); Compact travel adapter (10.5 oz/299 g); Charges with multiple PD voltage profiles (5V/9V/12V/15V/20V/28V at up to 5A); 6ft (1.8m) 240W EPR USB-IF Certified USB Type-C Cable Included
- **USB-IF CERTIFIED & EPR READY:** Power Adapter and included USB-C Cable are USB-IF certified for safe & reliable charging; Supports high-performance PD 3.1 with EPR for charging 140W devices like MacBook M3 Pro/Max; Future-proof for next-gen laptops
- **16" MACBOOK PRO COMPATIBLE:** PD 3.1 Power Adapter fully supports MacBook M3 Pro/Max ensuring high-speed 140W charging; Charges all USB-C devices with earlier PD revisions like MacBook, Dell XPS/Precision/Inspiron, iPad Pro, iPhone & Samsung smartphones
- **COMPACT & COOL RUNNING:** Engineered for cool performance under extended full-load use, with a foldable North American power plug (NEMA 1-15P) that enhances portability and easy storage; Small footprint (2.6 in/6.8cm x 1.2in/3.1cm x 3in/7.8cm)
- **SAFE, RELIABLE & EFFICIENT:** Designed to keep users & devices safe; TUV Safety Listed (IEC 62368-1) & FCC/ICES EMC certified; Over-voltage, current, and temp. protection; Active Power Factor Correction (PF > 0.99); Meets DOE Level VI standards

Hardware

Garantiebestimmungen 2 Years

Steckdosenkompatibilität 1
ät

Industrienormen USB Power Delivery 3.1

Steckverbinder

Eingangssteckverbinder 1 - NEMA 1-15 Strom (Nordamerika)

Ausgangssteckverbinder 1 - USB Typ-C (24-polig) Nur USB Power Delivery

r

Strom

Eingangsspannung	100 - 240 AC
Eingangsstrom	2.0A
Ausgangsspannung	15V DC
	5V DC
	9V DC
	12V DC
	20V DC
	28V DC
Ausgangsstrom	3A (5V, 9V, 12V, 15) / 5A (20V, 28V)
Steckertyp	NEMA 1-15 Power (North America) Plug
Stromverbrauch	140 W

Umgebungsbedingungen

Betriebstemperatur	0 to 25°C (32 to 77°F)
Lagertemperatur	-20 to 80°C (-4 to 176°F)
Feuchtigkeit	Operation: 10% ~ 90% RH
	Storage: 30% ~ 90% RH

Physische Eigenschaften

Farbe	Schwarz
Gehäusety	Kunststoff
Produktlänge	2.7 in [6.8 cm]
Produktbreite	1.2 in [3.1 cm]
Produkt	3.1 in [7.8 cm]

Produktgewicht 10.6 oz [299.0 g]

Verpackungsinformationen

Paketlänge 3.4 in [8.6 cm]
Paketbreite 6.3 in [16.1 cm]
Pakethöhe 1.5 in [3.8 cm]
Versandgewicht (Verpackung) 14.3 oz [404.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - USB-Wandladegerät
1 - 6 ft. [1.8m] USB-C Cable (240W)
1 - Kurzanleitung

Garantieinformationen

Warranty 2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.