

Brocade 10G-SFPP-SR Compatible SFP+ Module - 10GBASE-SR - 10GbE Multimode Fiber MMF
Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 200m - 850nm - DDM

Product ID: 10G-SFPP-SR-ST



The 10G-SFPP-SR-ST is a Brocade 10G-SFPP-SR compatible fiber transceiver module that has been designed, programmed and tested to work with Brocade brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-SR compliant networks, with a maximum distance of up to 200 m (656 ft).

Technical Specifications:

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 200 m (656 ft)
- MTBF: 498,745,585 hours
- Power Consumption: < 1W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% BROCADE 10G-SFPP-SR COMPATIBLE SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible Brocade switches and routers to deliver dependable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-SR 10Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 200m (656ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Brocade routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	Brocade
Industry Standards	IEEE 802.3ae 10GBASE-SR

Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	200 m (656 ft)
Type	Multi Mode
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	498,745,585 hours
Power Consumption (In	< 1W

Watts)

**Physical
Characteristics**

Product Length	0.5 in [13.9 mm]
Product Width	2.3 in [58.4 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	0.7 oz [20 g]

**Packaging
Information**

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	SFP+ Transceiver
---------------------	------------------

**Product appearance and specifications are subject to change without notice.*

