

UL Listed Extendable TV Wall Mount for up to 105inch 176lb (80kg) Display, Easy Rear Access, Laterally Adjustable Bracket Supports up to VESA 1000x600

Product ID: 10ULE-TV-WALL-MOUNT



UL listed TV mount supports up to 105-inch displays and 176lb (80kg), giving you a sturdy platform with anti-theft design for meeting rooms, classrooms, and digital signage that need a strong, stable wall bracket. Keep the TV close to the wall at a 2.1in (5.3cm) profile or extend up to 6.8in (17.2cm) to match your setup.

This TV mount is tested and certified by UL Solutions to UL 2442 and complies with a 4x weight safety factor over its rated load, providing assurance for commercial and public-space installations

The extendable arms create ample working room behind the TV, providing easy access to AV, power, and network connections for cable installation and reconfiguration. Integrated quick-release cords allow the display to be removed and reinstalled quickly for servicing when needed.

Use the side-to-side sliding design to help center the display on wood stud, concrete, or brick walls. VESA compatibility from 200x200 to 1000x600mm helps standardize installs across a wide range of TVs.

Fine-tune the viewing angle with tilt from +10 to -15 and swivel from +10 to -10 to improve visibility across the room.

Certifications, Reports and Compatibility

Applications

Features

- **Securely Mount Large, Heavy Displays**: This UL listed TV mount supports up to 105-inch displays and 176lb (80kg), giving you a sturdy platform with anti-theft design for meeting rooms, classrooms, and digital signage

- **Mount with Confidence**: This TV mount is tested and certified by UL Solutions to UL 2442 and complies with a 4x weight safety factor over its rated load, providing assurance for commercial and public-space installations
- **Easy Service Access**: Extendable arms reach up to 6.8in (17.2cm), creating ample space for rear TV access and cable management; Integrated quick-release cords make it easy to remove and reinstall the display for servicing and maintenance
- **Center the TV on Any Wall Type**: Use the side-to-side sliding design to center the TV on wood stud, concrete, or brick walls, while VESA compatibility from 200x200 to 1000x600 enables supports for a wide range of displays
- **Adjust the Screen for Better Viewing**: Adjustable TV bracket lets you fine-tune positioning with tilt from +10 to -15 and swivel from +10 to -10 for better visibility across the room

Hardware

Warranty	5 Years
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	2.1 in [53 mm]
VESA Hole Pattern(s)	200x200 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600x400 mm
	600x600 mm
	800x400 mm
	800x600 mm
	900x600 mm
	1000x600 mm

Performance

Minimum Display Size	55"
----------------------	-----

Maximum Display Size	105"
Video Wall	No
Height Adjustment	Yes
Maximum Arm Span	6.8 in [172 mm]
Display Tilt	+10 / -15
Display Swivel	+10 / -10
Anti-theft	Yes

Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	42.1 in [1070 mm]
Product Width	2.1 in [53 mm]
Product Height	13.8 in [350 mm]
Weight of Product	651.3 oz [18450 g]

Packaging Information

Package Length	5.2 in [13.3 cm]
Package Width	3.7 ft [1.1 m]
Package Height	3.0 in [7.5 cm]
Shipping (Package) Weight	14.9 lb [6.8 kg]

What's in the Box

Included in Package	1 - TV Mounting Assembly, Right
	1 - TV Mounting Assembly, Left
	2 - Horizontal Brackets
	2 - Vertical Brackets

- 1 - Spirit/Buble Level
- 1 - 4mm Hex Key
- 1 - 6mm Hex Key
- 1 - Wrench
- 4 - M6x8mm Screws
- 4 - M6x14mm Screws
- 4 - M8x16mm Screws
- 4 - M6x30mm Screws
- 4 - M8x35mm Screws
- 4 - Washers
- 4 - Short Spacers
- 4 - Long Spacers
- 6 - Wall Mounting Screws
- 6 - Wall Anchors
- 6 - Wall Mounting Washers
- 1 - Wall Mounting Template
- 1 - Product Documentation

****Product appearance and specifications are subject to change without notice.***