

major operating systems, including Windows, macOS, ChromeOS, and Ubuntu. This dock was designed for seamless integration with any compatible USB-C equipped device within your organization, including Lenovo X1/Thinkpad P Series, Dell Latitudes/Precision/XPS 15, HP Envy, Surface Laptop 3, and M1 Pro/Max/M2 MacBooks. The dock features a side-facing K-Slot for added security in shared workspaces (e.g., BYOD hoteling/hot-desking).

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: Setup and save custom windows layouts.

Mac Address Pass-Through Utility: Improve network security.

USB Event Monitoring Utility: Track and log connected USB devices.

Wi-Fi Auto Switch Utility: Enable users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/Connectivity-Tools

This product is backed for 3-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Use in laptop hot-desk workstations for hoteling
- Charge your tablets and smartphones from the B.C 1.2 USB ports

Features

- Universal USB-C Dock: High-performance dock works with all major operating systems such as Windows, MacOS, ChromeOS and Ubuntu; Ideal for mixed-device fleets and laptop refresh cycles, simplifying standardization, and user onboarding across departments
- GPU Agnostic: Bypass GPU limitations for multi-monitor setups, maximize ROI, and future-proof your IT

infrastructure with a dock that ensures compatibility across all hardware platforms, including Intel, Apple Silicon, AMD, and Snapdragon X Copilot+ PCs

- **Triple 4K Displays for Expanded Productivity:** Connect up to three 4K monitors through a single USB C port; This dock supports two 4K 60Hz monitors via DisplayLink (HDMI 2.0 or DisplayPort 1.2) and a third 4K 30Hz HDMI display through DP 1.2 Alt Mode
- **100W Power Delivery:** Docking station includes a fully spec'd power adapter to charge the host laptop while supplying power across all ports; Downstream USB and USB-C ports deliver up to 7.5W (1.5A) for mobile or battery-powered devices
- **The IT Pro's Choice:** Our docking stations are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments, Windows 11 upgrades, and the shift to AI-enabled PCs

General

UPC	065030900096
Package Quantity	1
Warranty	3 Years

Special Notes / Requirements

Special Notes	Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure your host device's USB-C port supports USB Power Delivery and DP alt mode. A 4K-capable display is required to achieve 4096 x 2160p/3840 x 2160p resolution. A 4K-capable computer is required to achieve 3840 x 2160p resolution (4K is also known as 4K x 2K) on the DP Alt-Mode HDMI port. USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps) and USB 3.0 (5Gbps).
System and Cable Requirements	A host device with an available USB-C port (to ensure full adapter functionality, the host device's USB-C port must support USB Power Delivery 2.0 and DP alt mode).

Power

Power Source	AC Adapter Included
Power Delivery	100W
Input Voltage	110V-240V AC
Input Current	2.5 A

Output Voltage	24 DC
Output Current	5.41
Center Tip Polarity	Positive
Plug Type	M
Power Consumption	15W

Physical & Environmental

Color	Space Gray
Material	Plastic
Cable Length	38.8 in [985 mm]
Product Length	7.5 in [190.0 mm]
Product Width	3.3 in [85.0 mm]
Product Height	1.2 in [30.0 mm]
Weight of Product	9.5 oz [270 g]
Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	0~85% RH (Non-condensing)

Performance

Device Power Consumption	985
Supported Charging Outputs	BC 1.2 (1.5A)
Maximum Data Transfer Rate	10Gbps
Type and Rate	USB 10Gbps
Compatible Networks	10/100/1000 Mbps
Wake-On-LAN (WOL)	Yes
MTBF	44,877 Hours

Maximum Digital Resolutions	2x HDMI and/or DisplayPort: 4K (4096 x 2160) 60Hz
	1x HDMI (via DP Alt Mode): 4K (4096 x 2160) 30Hz

Hardware

Fast-Charge Port(s)	Yes
4K Support	Yes
Displays Supported	3
Number of Battery Charge 1.2 Ports	2
Audio	Yes
Interface	USB 3.2 Gen 2 10Gbps
Bus Type	USB 3.2 Gen 2
Compatible Lock Slot	Kensington Standard Slot (K-Slot)
Number of Displays	3
Industry Standards	HDMI 2.0
	DisplayPort 1.4
	USB 3.2 Gen 2 (10Gbps)
	USB 3.2 Gen 1 (5Gbps)
	1000Base-T, 100Base-TX, 10Base-T (IEEE802.3ab compliant)
Chipset ID	DisplayLink - DL-6950-N
	VIA - VL817C0
	Parade - PS176C0
LED Indicators	1 - Power LED (white)

Packaging & In-the-Box

Included in Package	1 - USB-C Docking Station
	1 - 3 ft [1 m] USB-C Host Cable
	1 - Power Adapter (UK)

1 - Quick-Start Guide

Package Width	9.8 in [250 mm]
Package Depth	8.1 in [205 mm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	40.1 oz [1135 g]

Connector(s)

Host Connector 1 (Quantity)	1
Host Connector 1	USB-C (10Gbps, 4.5W)
Connector 1 (Quantity)	3
Connector 1	HDMI
Connector 2 (Quantity)	2
Connector 2	DisplayPort
Connector 3 (Quantity)	1
Connector 3	USB-A (10Gbps, 7.5W)
Connector 4 (Quantity)	1
Connector 4	USB-A (10Gbps, 7.5W)
Connector 5 (Quantity)	1
Connector 5	USB-C (5Gbps, 4.5W)
Connector 6 (Quantity)	2
Connector 6	USB-A (5Gbps, 4.5W)
Connector 7 (Quantity)	1
Connector 7	3.5mm (4 Conductors, TRRS)
Connector 8 (Quantity)	1
Connector 8	RJ-45

**Product appearance and specifications are subject to change without notice.*