

13-Outlet Rackmount PDU, 1U Server Power Strip with 1x Front and 12x Rear Ports, Mounted Power Distribution Unit for 19-Inch Racks and Cabinets

Product ID: 1315B8H-RACK-PDU



Deliver reliable power to critical equipment in server rooms, AV racks, and test benches. This 1U rackmount PDU features 13 NEMA 5-15 electrical, a built-in circuit breaker, and versatile mounting options, making it a dependable power backbone for critical deployments.

Designed for dense IT and AV environments this unit powers up to 13 devices through 1x front and 12x rear-facing NEMA 5-15 outlets. The built-in 8ft (2.4m) power cord provides the flexibility and reach needed to accommodate various configurations.

The integrated 15A circuit breaker helps protect connected equipment by automatically cutting power if the total current draw exceeds safe operating limits.

Power delivery unit is TAA-compliant and includes 4-way mounting brackets that provide flexibility for horizontal or vertical mounting. The PDU is compatible with standard 19" EIA-310 racks that are at least 4in (10.1cm) deep and is constructed from durable, powder-coated SPCC steel for long-term reliability.

Certifications, Reports and Compatibility

Applications

Features

- **Centralized Rack Power:** This rack mounted power distribution unit delivers reliable 120V power for up to 13 devices, ideal for small to mid-sized IT environments, offices, and businesses needing an organized and efficient distribution system

- **Support Flexible Access:** Built-in NEMA 5-15 outlets feature 1 front-facing port for quick connections and 12 rear-facing ports for clean cable routing in various rack configurations; 8ft (2.4m) power cord easily reaches distant AC outlets
- **Mount Where You Need It:** TAA-compliant 1U PDU installs horizontally or vertically on EIA-310 19" racks or cabinets over 4in (10.1cm) deep with the included 4-way brackets; Rugged SPCC steel housing with powder-coated finish ensures long-term durability
- **Protect Equipment with Circuit Breaker:** A user-resettable 15A breaker safeguards connected devices from overloads
- **The IT Pro's Choice:** Our rack-mount PDUs are lab-tested to ensure enterprise-grade reliability for continuous uptime and optimal performance in edge, on-prem, AV racks, and data center deployments; Backed by free lifetime 24/5 technical assistance

Hardware

Warranty	2 Years
U Height	1U

Power

Input Voltage	120 AC
Plug Type	NEMA 5-15 Power (North America) Plug

Physical Characteristics

Color	Black
Material	Steel
Product Length	18.8 in [477.2 mm]
Product Width	4.3 in [110 mm]
Product Height	1.7 in [43.3 mm]
Weight of Product	59.7 oz [1690 g]

Packaging Information

Package Length	9.3 in [23.5 cm]
Package Width	20.3 in [51.6 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package)	4.8 lb [2.2 kg]

Weight

What's in the Box

Included in Package	1 - Rack-Mount PDU
	2 - Mounting Brackets (Pre-Installed)
	4 - M5 Cage Nuts
	4 - M5x12mm Rack Screws
	4 - Plastic Washers
	4 - Metal Washers
	1 - Product Documentation

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

