

Câble IEEE-1394 FireWire 4-6 M/M

N° de produit: 139446MM1



This 1ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV Camcorder to a computer, etc.).

Certifications, rapports et compatibilité

Applications

- Connect a external FireWire hard drive enclosure to a Notebook or PC
- Connect a FireWire camera or video recorder to a Notebook or PC
- Perfect for portable FireWire applications

Spécifications techniques

- Molded connector strain relief
- Short, portable cable design
- IEEE 1394a Standards Compliant

Matériel

Politique de garantie	Lifetime
Type de gaine de câble	PVC - Polyvinyl Chloride
Type de blindage du câble	Feuille d'aluminium-Mylar avec blindage tressé

Performance

Type et débit	FireWire 400 IEEE-1394a - 400 Mbit/s
---------------	--------------------------------------

Connecteur(s)

Connecteur A	FireWire 400 (4 broches , IEEE 1394a)
Connecteur B	FireWire 400 (6 broches , IEEE 1394a)

Caractéristiques physiques

Couleur	Noir
Calibre du fil	30 AWG
Longueur de câble	12.0 in [30.5 cm]
Longueur du produit	12.0 in [30.5 cm]

Informations d'emballage

Package Length	4.9 in [12.5 cm]
Package Width	0.5 in [12.5 mm]
Package Height	8.6 in [21.9 cm]
Poids brut	1.8 oz [50 g]

Contenu du paquet

Inclus dans le paquet	1 Ft. IEEE-1394 Firewire Cable 4-6 Pin
-----------------------	--

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis