

1 ft IEEE-1394 FireWire Cable 4-6 M/M

Productcode: 139446MM1



This 1ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV Camcorder to a computer, etc.).

Certificaties, rapporten en compatibiliteit



Toepassingen

- Connect a external FireWire hard drive enclosure to a Notebook or PC
- Connect a FireWire camera or video recorder to a Notebook or PC
- Perfect for portable FireWire applications

Eigenschappen

- Molded connector strain relief

- Short, portable cable design
- IEEE 1394a Standards Compliant

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Prestaties

Type en snelheid	FireWire 400 IEEE-1394a - 400 Mbit/s
------------------	--------------------------------------

Connector(en)

Connector A	1 - Firewire 400 (4-polig, IEEE 1394a)
Connector B	1 - Firewire 400 (6-polig, IEEE 1394a)

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	30 AWG
Kabellengte	1.0 ft [0.3 m]
Lengte product	1.0 ft [0.3 m]

Verpakkingsinformatie

Lengte Verpakking	4.9 in [12.5 cm]
Package Width	0.5 in [12.5 mm]
Package Height	8.6 in [21.9 cm]
Verzendgewicht (verpakt)	1.8 oz [50 g]

Wat wordt er meegeleverd

Meegeleverd	1 - 1 Ft. IEEE-1394 Firewire Cable 4-6 Pin
-------------	--

Garantiebepalinge
n

Warranty

Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.