

1 ft IEEE-1394 FireWire Cable 4-6 M/M

Product ID: 139446MM1



This 1ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV Camcorder to a computer, etc.).

Certifications, Reports and Compatibility

Applications

- Connect a external FireWire hard drive enclosure to a Notebook or PC
- Connect a FireWire camera or video recorder to a Notebook or PC
- Perfect for portable FireWire applications

Features

- Molded connector strain relief
 - Short, portable cable design
 - IEEE 1394a Standards Compliant
-

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	FireWire 400 IEEE-1394a - 400 Mbit/s
---------------	--------------------------------------

Connector(s)

Connector A	FireWire 400 (4 pin, IEEE 1394a)
Connector B	FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Black
Wire Gauge	30 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]

Packaging Information

Package Length	4.9 in [12.5 cm]
Package Width	0.5 in [12.5 mm]
Package Height	8.6 in [21.9 cm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	1 Ft. IEEE-1394 Firewire Cable 4-6 Pin
---------------------	--

****Product appearance and specifications are subject to change without notice.***

