

10 ft IEEE-1394 FireWire Cable 6-6 M/M

Productcode: 1394_10



This 10ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Certificaties, rapporten en compatibiliteit



Toepassingen

Eigenschappen

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	6

	Connectormateriaal	Nikkel
	Type kabelmantel	PVC - Polyvinyl Chloride
Connector(en)	Connector A	1 - Firewire 400 (6-polig, IEEE 1394a)
	Connector B	1 - Firewire 400 (6-polig, IEEE 1394a)
Fysieke eigenschappen	Kleur	Zwart
	Kabellengte	10.0 ft [3.0 m]
	Lengte product	10.0 ft [3.0 m]
	Breedte product	0.0 in [0 cm]
	Hoogte product	0.0 in [0 cm]
	Gewicht product	5.8 oz [165 g]
Verpakkingsinformatie	Verpakkingsaantal	1
	Lengte Verpakking	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Package Height	1.0 in [25 mm]
	Verzendgewicht (verpakt)	6.0 oz [170 g]
Wat wordt er meegeleverd	Meegeleverd	1 - 10 Ft IEEE-1394 FireWire Cable 6-6 M/M
Garantiebepalingen	Warranty	Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.