

10 ft IEEE-1394 FireWire Cable 6-6 M/M

Product ID: 1394_10



This 10ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Certifications, Reports and Compatibility



Applications

Features

Hardware

Warranty	Lifetime
Number of Conductors	6
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - FireWire 400 (6 pin, IEEE 1394a)
Connector B	1 - FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	0.0 in [0 mm]
Product Height	0.0 in [0 mm]
Weight of Product	5.8 oz [165 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	1.0 in [25 mm]
Shipping (Package) Weight	6.0 oz [170 g]

What's in the Box

Included in Package	1 - 10 Ft IEEE-1394 FireWire Cable 6-6 M/M
---------------------	--

**Product appearance and specifications are subject to change without notice.*