

15 ft IEEE-1394 FireWire Cable 6-6 M/M

Product ID: 1394_15



This 15ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

Certifications, Reports and Compatibility



Applications

Features

Hardware

Warranty	Lifetime
Number of Conductors	6
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Cable Length	14.0 ft [4.3 m]
----------------------	-----------------

Connector(s)

Connector A	1 - FireWire 400 (6 pin, IEEE 1394a)
Connector B	1 - FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Black
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.4 cm]
Package Width	0.7 in [17 mm]
Package Height	11.4 in [29 cm]
Shipping (Package) Weight	10.9 oz [310 g]

What's in the Box

Included in Package	1 - 15 Ft IEEE-1394 FireWire Cable 6-6 M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***