

15 ft Transparent IEEE-1394 Firewire Cable 6-6 M/M

Product ID: 1394_15T



This 15ft transparent/clear IEEE-1394 rated FireWire cable provides the high-speed link required for today's demanding peripherals.

The cable features 6-pin FireWire connectors on both ends and see-through sheathing that blends quietly into any environment.

Compatible with all 6-pin FireWire and iLink devices.

Certifications, Reports and Compatibility



Applications

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

Features

- Transparent color blends into any environment
- Up to 400 Mbits/sec data transfer rate
- Supports Plug and Play

- Hot Pluggable; allows swapping of live devices
- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Supports a daisy-chain of up to 63 firewire devices
- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference
- 6-pin cable draws power from firewire bus

Hardware

Warranty	Lifetime
Number of Conductors	6
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Industry Standards	IEE1394-1995

Connector(s)

Connector A	1 - FireWire 400 (6 pin, IEEE 1394a)
Connector B	1 - FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Transparent
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]

Packaging Information

Package Length	4.9 in [12.5 cm]
Package Width	1.1 in [29 mm]
Package Height	8.3 in [21.2 cm]
Shipping (Package) Weight	10.6 oz [300 g]

What's in the Box

Included in Package	1 - 15 ft.Transparent FireWire Cable 6-6 Pin
---------------------	--

**Warranty
Information**

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***