

## 6 ft IEEE-1394 FireWire Cable 4-6 M/M

Productcode: 1394\_46\_6



This 6ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

### Certificaties, rapporten en compatibiliteit

### Toepassingen

### Eigenschappen

---

#### Prestaties

Garantiebeleid	Lifetime
Maximale kabellengte	14.0 ft [4.3 m]

---

#### Connector(en)

Connector A	Firewire 400 (4-polig, IEEE 1394a)
-------------	------------------------------------

Connector B Firewire 400 (6-polig, IEEE 1394a)

---

Fysieke eigenschappen

Kleur	Zwart
Kabellengte	6.0 ft [1.8 m]
Lengte product	6.0 ft [1.8 m]

---

Verpakkingsinformatie

Package Length	4.8 in [12.2 cm]
Package Width	0.5 in [13.2 mm]
Package Height	8.5 in [21.7 cm]
Verzendgewicht (verpakt)	3.5 oz [100 g]

---

Wat wordt er meegeleverd

Meegeleverd	6 Ft. IEEE-1394 FireWire Cable 4-6 Pin
-------------	--

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

