

6 ft IEEE-1394 FireWire Cable 4-6 M/M

Product ID: 1394_46_6



This 6ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

Certifications, Reports and Compatibility

Applications

Features

Performance

Warranty	Lifetime
Maximum Cable Length	14.0 ft [4.3 m]

Connector(s)

Connector A	FireWire 400 (4 pin, IEEE 1394a)
Connector B	FireWire 400 (6 pin, IEEE 1394a)

**Physical
Characteristics**

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]

**Packaging
Information**

Package Length	4.8 in [12.2 cm]
Package Width	0.5 in [13.2 mm]
Package Height	8.5 in [21.7 cm]
Shipping (Package) Weight	3.5 oz [100 g]

What's in the Box

Included in Package	6 Ft. IEEE-1394 FireWire Cable 4-6 Pin
---------------------	--

****Product appearance and specifications are subject to change without notice.***

