

## 6ft IEEE-1394 FireWire Cable 6-6 M/M

Produkt ID: 1394\_6



This 6ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

### Certifikat, rapporter och kompatibilitet

### Användning

### Funktioner

---

#### Prestanda

Garantipolicy	Lifetime
Maximal kabellängd	14.0 ft [4.3 m]

---

#### Kontakt(er)

Connector A	FireWire 400 (6-stifts, IEEE 1394a)
-------------	-------------------------------------

Connector B FireWire 400 (6-stifts, IEEE 1394a)

---

Utseende

Färg	Grå
Kabellängd	6.0 ft [1.8 m]
Produktlängd	6.0 ft [1.8 m]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	4.1 oz [115.0 g]

---

Förpackning

Package Length	5.0 in [12.6 cm]
Package Width	0.6 in [15.2 mm]
Package Height	8.3 in [21.0 cm]
Fraktvikt (förpackning)	4.1 oz [115.0 g]

---

Vad det är i lådan

Ingår i paketet	FIREWIRE CABLE
-----------------	----------------

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

