

6ft IEEE-1394 FireWire Cable 6-6 M/M

Product ID: 1394_6



This 6ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

Certifications, Reports and Compatibility



Applications

Features

Performance

Warranty	Lifetime
Maximum Cable Length	14.0 ft [4.3 m]

Connector(s)

Connector A	1 - FireWire 400 (6 pin, IEEE 1394a)
-------------	--------------------------------------

Connector B 1 - FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Gray
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	4.1 oz [115.0 g]

Packaging Information

Package Quantity	1
Package Length	5.0 in [12.6 cm]
Package Width	0.6 in [15.2 mm]
Package Height	8.3 in [21.0 cm]
Shipping (Package) Weight	4.1 oz [115.0 g]

What's in the Box

Included in Package	1 - FIREWIRE CABLE
---------------------	--------------------

**Product appearance and specifications are subject to change without notice.*