

10 ft IEEE-1394 FireWire 800 Cable 9-4 M/M

ID del Producto: 1394_94_10



This 10ft 1394b FireWire cable provides one FireWire 800 9-pin male connector and one FireWire 4-pin male connector, allowing you to connect your FireWire 400 devices to your FireWire 800 ports - ensuring that your high speed digital storage and video capture applications will be running at their peak.

Expertly designed to provide a high quality, long-lasting FireWire connection, the 1394b FireWire (4 pin to 9 pin) cable is backed by StarTech.com's Lifetime Warranty.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

Características

- Fast data transfer rate of up to 800 Mbits/sec

- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards
- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Hardware

Política de Garantía	Lifetime
Estándares Industriales	IEEE 1394a & 1394b

Rendimiento

Longitud Máxima del Cable	14.0 ft [4.3 m]
---------------------------	-----------------

Conector(es)

Conector A	1 - Firewire 800 (9 pines, IEEE 1394b)
Conector B	1 - Firewire 400 (4 pines, IEEE 1394a)

Características Físicas

Color	Negro
Longitud del Cable	10.0 ft [3.0 m]
Longitud del Producto	10.0 ft [3.0 m]
Peso del Producto	4.1 oz [115 g]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	7.8 in [19.9 cm]
Ancho de la Caja	0.7 in [18 mm]
Altura de la Caja	8.3 in [21.1 cm]

Peso (de la Caja) del 4.1 oz [116 g]
Envío

Contenido de la
Caja

Incluido en la Caja 1 - 10 ft IEEE-1394 FireWire 800 Cable 9-4 M/M

Información Acerca
de la Garantía

Warranty De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.