

10 ft IEEE-1394 FireWire 800 Cable 9-4 M/M

Productcode: 1394_94_10



This 10ft 1394b FireWire cable provides one FireWire 800 9-pin male connector and one FireWire 4-pin male connector, allowing you to connect your FireWire 400 devices to your FireWire 800 ports - ensuring that your high speed digital storage and video capture applications will be running at their peak.

Expertly designed to provide a high quality, long-lasting FireWire connection, the 1394b FireWire (4 pin to 9 pin) cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

Eigenschappen

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards

- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Hardware

Garantiebeleid	Lifetime
Industriestandaarden	IEEE 1394a & 1394b

Prestaties

Maximale kabellengte	14.0 ft [4.3 m]
----------------------	-----------------

Connector(en)

Connector A	Firewire 800 (9-polig, IEEE 1394b)
Connector B	Firewire 400 (4-polig, IEEE 1394a)

Fysieke eigenschappen

Kleur	Zwart
Kabellengte	10.0 ft [3.0 m]
Lengte product	10.0 ft [3.0 m]
Gewicht product	4.1 oz [115 g]

Verpakkingsinformatie

Package Length	7.8 in [19.9 cm]
Package Width	0.7 in [18 mm]
Package Height	8.3 in [21.1 cm]
Verzendgewicht (verpakt)	4.1 oz [116 g]

Wat wordt er meegeleverd

Meegeleverd	10 ft IEEE-1394 FireWire 800 Cable 9-4 M/M
-------------	--



* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

