

6 ft IEEE-1394 FireWire Cable 9-4 M/M

Product ID: 1394_94_6



This 6ft 1394b FireWire cable provides one FireWire 800 9-pin male connector and one FireWire 4-pin male connector, allowing you to connect your FireWire 400 devices to your FireWire 800 ports - ensuring that your high speed digital storage and video capture applications will be running at their peak.

Expertly designed to provide a high quality, long-lasting FireWire connection, the 1394b FireWire (4 pin to 9 pin) cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards

- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

Hardware

Warranty	Lifetime
Industry Standards	IEEE 1394a & 1394b

Performance

Maximum Cable Length	14.0 ft [4.3 m]
----------------------	-----------------

Connector(s)

Connector A	1 - FireWire 800 (9 pin, IEEE 1394b)
Connector B	1 - FireWire 400 (4 pin, IEEE 1394a)

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]

Packaging Information

Package Quantity	1
Package Length	8.0 in [20.2 cm]
Package Width	0.4 in [11 mm]
Package Height	8.5 in [21.5 cm]
Shipping (Package) Weight	3.2 oz [90 g]

What's in the Box

Included in Package	1 - 6 ft IEEE-1394 FireWire Cable 9-4 M/M
---------------------	---

Warranty

Information

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*