

6 ft IEEE-1394 FireWire Cable 9-6 M/M

Productcode: 1394\_96\_6



This 6ft IEEE 1394b FireWire 800 Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 800Mbps, FireWire 800 (IEEE 1394b) technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

This high quality FireWire 800 (9 to 6-pin) cable compatible with all 1394a & 1394b PC FireWire (400/800), Apple FireWire, and Sony iLink devices and is backed by StarTech.com's Lifetime Warranty.

## Certificaties, rapporten en compatibiliteit

## Toepassingen

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

## Eigenschappen

- Fast data transfer rate of up to 800 Mbits/sec

- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards
- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

---

#### Hardware

|                      |                   |
|----------------------|-------------------|
| Garantiebeleid       | Lifetime          |
| Industriestandaarden | IEEE 1394a, 1394b |

---

#### Connector(en)

|             |                                    |
|-------------|------------------------------------|
| Connector A | Firewire 800 (9-polig, IEEE 1394b) |
| Connector B | Firewire 400 (6-polig, IEEE 1394a) |

---

#### Fysieke eigenschappen

|                 |                  |
|-----------------|------------------|
| Kleur           | Zwart            |
| Kabellengte     | 6.0 ft [1.8 m]   |
| Lengte product  | 6.0 ft [1.8 m]   |
| Breedte product | 0.0 in [0.0 mm]  |
| Hoogte product  | 0.0 in [0.0 mm]  |
| Gewicht product | 3.8 oz [106.7 g] |

---

#### Verpakkingsinformatie

|                          |                  |
|--------------------------|------------------|
| Package Length           | 7.8 in [19.9 cm] |
| Package Width            | 0.7 in [17.0 mm] |
| Package Height           | 8.3 in [21.1 cm] |
| Verzendgewicht (verpakt) | 3.8 oz [107.7 g] |



---

Wat wordt er  
meegeleverd

Meegeleverd

6 ft IEEE-1394 FireWire Cable 9-6 M/M

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

