

3ft (1m) Power Extension Cord, IEC 320 C14 to NEMA 5-15R, 10A 125V, 18AWG, Black
Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/ PDUs /
Network Equipment

Produkt-ID: 1415R-3F-POWER-CORD



High-Quality Construction

The universal monitor power cord is built with 18 AWG wire and rated to carry 125V at 10A. It is constructed with fully molded strain relief connectors, ensuring a reliable and durable connection for your devices.

Universal Replacement Cable

This replacement power cord features an IEC 320 C14 to NEMA 5-15R connector and is compatible with most monitors, PCs, scanners, and printers.

Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **AC COMPUTER POWER CABLE:** This 3ft (1m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home offices | Indoor use only | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord made with 100% copper wire | This power extension cord is available in other lengths
- **SPECIFICATIONS:** 3ft (1m) AC Power Cord | IEC 60320 C14 to NEMA 5-15R | 18AWG | 125V 10A (Max) | Jacket Type: SVT | Jacket Material: PVC | Black | Temperature Range: 14 to 95°F (-10 to 35°C) | Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables | Extend a 3-prong NEMA 5-15P power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen Lifetime

Steckverbinderplatten Nickel

Steckverbinder

Steckverbinder A 1 - IEC 60320 C14 Strom

Steckverbinder B 1 - NEMA 5-15 Strom (Nordamerika)

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 18 AWG

Kabellänge 3.0 ft [0.9 m]

Produktlänge	1.1 in [2.7 cm]
Produktbreite	36.0 in [91.5 cm]
Produkthöhe	1.2 in [3.0 cm]
Produktgewicht	4.0 oz [114.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.7 cm]
Paketbreite	3.1 in [7.9 cm]
Pakethöhe	1.5 in [3.8 cm]
Versandgewicht (Verpackung)	4.3 oz [122.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - Computerstromkabel
--------------------	------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.