

3ft (1m) Power Extension Cord, IEC 320 C14 to NEMA 5-15R, 10A 125V, 18AWG, Black Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/ PDUs / Network Equipment

Product ID: 1415R-3F-POWER-CORD



High-Quality Construction

The universal monitor power cord is built with 18 AWG wire and rated to carry 125V at 10A. It is constructed with fully molded strain relief connectors, ensuring a reliable and durable connection for your devices.

Universal Replacement Cable

This replacement power cord features an IEC 320 C14 to NEMA 5-15R connector and is compatible with most monitors, PCs, scanners, and printers.

Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **AC COMPUTER POWER CABLE:** This 3ft (1m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home offices. Indoor use only. Rated to carry 125V at 10A.
- **PERFORMANCE AND SAFETY:** Fully molded strain relief connectors for durability. Fire Rating: VW-1. 3 Conductor extension cord made with 100% copper wire. This power extension cord is available in other lengths.
- **SPECIFICATIONS:** 3ft (1m) AC Power Cord. IEC 60320 C14 to NEMA 5-15R. 18AWG. 125V 10A (Max). Jacket Type: SVT. Jacket Material: PVC. Black. Temperature Range: 14 to 95F (-10 to 35C). Cable Outer Diameter: 0.25in (6.3mm).
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables. Extend a 3-prong NEMA 5-15P power connection from your desktop computer, server, or printer. Replacement power supply cable/cord.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - NEMA 5-15 Power (North America)

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	1.1 in [2.7 cm]
Product Width	36.0 in [91.5 cm]
Product Height	1.2 in [3.0 cm]
Weight of Product	4.0 oz [114.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	5.7 in [14.5 cm]
Package Width	11.4 in [29.0 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	4.4 oz [124.0 g]

What's in the Box

Included in Package	1 - Computer Power Cord
---------------------	-------------------------

**Product appearance and specifications are subject to change without notice.*