

Replacement Universal AC/DC Power Adapter with NA Power Cord for Docking Stations - 150W (19.5V/7.7A)

Produkt-ID: 158-DOCKPOWERADAPTER



This 150W AC/DC power supply can provide a power source for any electronic device that has an N-type barrel and requires 19.5 volts and up to 7.7 amps of power.

The power supply is a perfect replacement for the lost or damaged 19.5-volt 7.7-amp power adapter you've used to power your existing electronics.

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This 19.5V 7.7A DC power supply is a direct replacement for the power adapters included with the following StarTech.com products:

DK30C2DPEP Laptop Docking Station

DK30C2DPPD Laptop Docking Station

DK31C3HDPD Laptop Docking Station

DK30CH2DEP Laptop Docking Station

DK30CH2DPPD Laptop Docking Station

DK30CHDDPPD Laptop Docking Station

DK30CHHPD Laptop Docking Station

DK30CHDPD Laptop Docking Station

MST30C2HHPD Laptop Docking Station

This product is backed for 3-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Replace a lost or broken 19.5V DC power supply
- Halten Sie einen zusätzlichen Netzadapter bereit für geschäftskritische Geräte

Merkmale

- REPLACEMENT POWER ADAPTER: Replaces the power adapter included with models of StarTech.com docking stations
- WORKS WITH: DK30C2DPEP, DK30C2DPPD and DK31C3HDPD laptop docking stations
- TECHNICAL SPECIFICATIONS: 150W Power Adapter - 100 - 240 AC Input Voltage - 19.5V Output Voltage - 7.7A Output Current - NEMA 1-15P - N-Barrel Connector (5.5 mm outside diameter / 2.5 mm inside diameter)
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this power adapter is backed for 3-years including free lifetime 24/5 multi-lingual technical assistance

Strom

Garantiebestimmungen 3 Years

Stromversorgung Mit Netzadapter

Frequenz 50 - 60Hz
Eingangsspannung

Max. Einschaltstrom 29% margin of the I2T (Ampere Squared Seconds)
rating of the input fuse and bridge rectifier

Eingangsspannung 100 - 240 AC

Eingangsstrom	2.5
Ausgangsspannung	19.5V DC
Ausgangsstrom	7.7A
Polarität der Mittelspitze	Positiv
Steckertyp	N
Stromverbrauch	150

Physische Eigenschaften

Produktlänge	2.6 in [6.5 cm]
Produktbreite	5.4 in [13.7 cm]
Produkthöhe	0.8 in [2.1 cm]
Produktgewicht	1.4 lb [0.6 kg]

Verpackungsinform ationen

Paketmenge	1
Paketlänge	7.9 in [20.0 cm]
Paketbreite	9.4 in [24.0 cm]
Pakethöhe	1.6 in [4.0 cm]
Versandgewicht (Verpackung)	1.4 lb [0.6 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Universeller Netzteil (NA)
--------------------	--------------------------------

Garantieinformatio nen

Warranty	3 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.