

15ft (4.5m) Heavy Duty Power Cord, NEMA 5-15P to Locking C13 AC Power Cable, 125V 15A, 14AWG, Replacement Computer/Monitor Power Cord, TAA Compliant, UL Listed

Product ID: 15FT-LC15A-POWERCORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Locking C13 connector hinders accidental power disconnection
- Connect a computer, display, or laptop power supply to a wall outlet or PDU

Features

- **Deliver Reliable Power**: Connect desktop PCs, monitors, and IT peripherals to a wall outlet or PDU using this 15ft (4.5m) NEMA 5-15P to Locking C13 AC power cord; Built with 14AWG 100% copper wire and rated for up to 125V at 15A for safe, indoor deployments
- **Minimize Power Interruptions**: Keep mission-critical devices powered with a locking C13 connector that resists unintentional unplugging due to vibration, tension, or handling; Ensure reliable power delivery to mounted equipment with limited access
- **Built and Certified for Safety**: UL Listed power cord for professional use with a VW-1 flame-rated jacket; Flexible SJT construction simplifies routing through compact racks and trays common in on-prem and edge data centers and server rooms
- **Replace Old Power Cords**: Replace worn or unreliable power cords with this locking C13 cable that stays securely connected; The NEMA 5-15P plug fits standard North American outlets, and the locking IEC 60320 C13 works with most PCs, monitors, and printers
- **The IT Pro's Choice**: Our power cords are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and compatibility across a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
	1 - NEMA 5-15 Power (North America)

Connector B 1 - IEC 60320 C13 Power

Power

Input Voltage	125 AC
Input Current	15A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	14 AWG
Cable Length	15.0 ft [4.6 m]
Cable OD	0.4 in [9.3 mm]
Product Length	15.0 ft [4.6 m]
Product Width	1.2 in [2.9 cm]
Product Height	1.0 in [2.6 cm]
Weight of Product	0.7 lb [0.3 kg]

Packaging Information

Package Length	5.4 in [13.8 cm]
Package Width	14.8 in [37.5 cm]
Package Height	2.0 in [5.0 cm]
Shipping (Package) Weight	1.5 lb [0.7 kg]

What's in the Box

Included in Package	1 - 15ft (4.5m) NEMA 5-15P to Locking C13 Power Cord
---------------------	--

**Warranty
Information**

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*