

160W Universal DC Power Adapter (24V/6.6A), 4ft(1.2m) 2-Wire Cord, 2/3-Pin Terminal Blocks, 100-240V AC/DC External Power Supply for Industrial USB Hubs, NA/UK/EU/ANZ

**Product ID:** 160W-POWER-ADAPTER



Power a StarTech.com Industrial USB Hub, or other device with a 2-or-3-wire terminal block DC input, using this 24V Universal Power Adapter.

The Power Adapter features an auto-switching 100-240V AC input with a 24V/6.6A (158.4W) DC output and attached 4ft (1.2m) DC cord.

Four 4ft (1.2m) regional power cables are included, to ensure international support:

- North America - Type-A NEMA 1-15
- United Kingdom - Type-G BS 1363
- Europe - CEE 7/7
- Australia/New Zealand - Type-I AS 3112

The Power Adapter features two bare-wire leads with both 2-conductor and 3-conductor terminal block connectors included, for seamless integration with a variety of devices. This power supply can be used as an accessory and primary power source for many StarTech.com Industrial USB Hubs, such as:

- 16-Port Industrial USB 5Gbps Hub (5G16AINDS-USB-A-HUB)
- 10-Port Industrial USB 5Gbps Hub (ST1030USBM)
- 7-Port Industrial USB 5Gbps Hub (ST7300USBME)
- 7-Port Industrial USB 2.0 (480Mbps) Hub (HB20A7AME)
- 7-Port Industrial USB 2.0 (480Mbps) Hub with Extended Temperature Range (ST7200USBM)

- 4-Port Industrial USB 2.0 (480Mbps) Hub with Extended Temperature Range (HB20A4AME)
- 4-Port Industrial USB 2.0 (480Mbps) Hub (ST4200USBM)

This power adapter can also be used to replace a lost or broken power adapter, or can be kept as a redundant back-up power brick for mission critical applications for StarTech.com Industrial USB Hubs that include a power adapter, such as:

- 10-Port USB 5Gbps Industrial Hub (HB30A10AME)
- 7-Port USB 5Gbps Industrial Hub (HB30A7AME)
- 4-Port Industrial USB 5Gbps Hub (ST4300USBM)

## Certifications, Reports and Compatibility



## Applications

- Add additional power to a bus-powered USB Hub to power/charge downstream USB devices
- Replace a lost or broken power adapter
- Keep a redundant back-up power brick on-hand in the event a mission-critical power source is interrupted

## Features

- **UNIVERSAL POWER ADAPTER:** 24V/6.6A (158.4W) DC output with attached 4ft (1.2m) DC cord; Auto-switching 100-240V AC input; Includes four regional 4ft (1.2m) AC power cables (NA: Type-A NEMA 1-15, UK: Type-G BS 1363, EU: CEE 7/7, ANZ: Type-I AS 3112)
- **VERSATILE TERMINAL BLOCK COMPATIBILITY:** The power adapter features bare-wire leads with both 2-and-3-conductor terminal block connectors included, for seamless integration with a wide range of equipment
- **DEVICE COMPATIBILITY:** This power supply supports a variety of devices including our Industrial USB Hubs, part numbers: HB30A10AME, HB30A7AME, ST1030USBM, ST7300USBME, ST4300USBM, HB20A7AME, ST7200USBM, HB20A4AME, ST4200USBM, 5G16AINDS-USB-A-HUB
- **APPLICATIONS:** Replace a lost/broken power adapter; Maintain a redundant backup power brick in case a mission-critical power source is interrupted; Add additional power to a compatible hub to enable BC 1.2 charging & powering higher power devices
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this External International Electrical Power Adapter is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

## Power

Warranty	2 Years
Input Voltage	100 - 240 AC
Input Current	3.5A
Output Voltage	24 DC
Output Current	6.6A
Plug Type	Terminal Block (2 Wire) Terminal Block (3 Wire)
Power Consumption (In Watts)	158.4W

---

## Environmental

Operating Temperature	5C to 55C (41F to 131F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	20% ~ 80% RH

---

## Physical Characteristics

Color	Black
Material	Plastic
Cable Length	4.0 ft [1.2 m]
Product Length	4.5 in [11.5 cm]
Product Width	2.1 in [5.3 cm]
Product Height	1.5 in [3.7 cm]
Weight of Product	10.3 oz [291.0 g]

---

## Packaging Information

Package Quantity	1
Package Length	3.5 in [9.0 cm]
Package Width	6.3 in [16.0 cm]

Package Height	7.9 in [20.0 cm]
Shipping (Package) Weight	12.4 oz [350.0 g]

---

**What's in the Box**

Included in Package	1 - Universal Power Adapter with 4ft [1.2m] Cable
	4 - 4ft [1.2m] Power Cords (NA/JP, EU, UK, ANZ)
	1 - Two Conductor Terminal Block Connector (Attached)
	1 - Three Conductor Terminal Block Connector
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***