

USB-C Multiport Adapter w/Attached USB-C to USB-A Dongle, Dual HDMI (4K30Hz/1080p60Hz), 3x USB-A 5Gbps, Mini Travel Dock, Laptop Docking Station, 1.3ft/40cm Cable

**Product ID:** 167B-USBC-MULTIPORT



This USB Type-C & USB Type-A Multiport Adapter turns almost any laptop or desktop into a high-productivity workstation that supports dual external HDMI displays and features a 3-port USB hub. The Mini Dock has a built-in 1.3ft (40cm) USB-C host cable and includes a tethered USB-C to USB-A adapter, so it can support both USB-C and USB-A host computers.

Enhance productivity with two HDMI output ports for connecting external monitors. The HDMI output ports support resolutions up to 4K 30Hz (Video Output 1, HDMI 1.4), and 1080p 60Hz (Video Output 2, HDMI 1.2). Dual external monitors increase productivity - enabling users to have different applications, documents, or windows open on each monitor.

The Multiport Adapter is compatible with Windows, macOS, and Chrome OS. With its tethered USB-C to USB-A dongle that ensures it ensures seamless USB compatibility with any host running a supported OS. The Multiport Adapter supports dual-extended displays on Apple M1/M2/M3 MacBooks, which are not capable of driving more than one external display natively.

The USB-C & USB-A Multiport Adapter features three downstream USB-A ports. For fast and reliable data transfers the built-in USB hub supports SuperSpeed USB 3.2 Gen 1 (5Gbps) and is backward compatible with legacy USB 2.0 and USB 1.1 (HID) devices.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that is compatible with a wide variety of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: Setup and save custom windows layouts.

USB Event Monitoring Utility: Track and log connected USB devices.

For more information and to download the StarTech.com Connectivity Tools application, please visit:  
[www.startech.com/connectivity-tools](http://www.startech.com/connectivity-tools)

## Certifications, Reports and Compatibility



## Applications

- Home office IT deployment, ideal for traveling between the home and office
- Run multiple applications on extended HDMI displays

## Features

- **INCREASED PRODUCTIVITY:** Multiport Adapter adds dual HDMI displays to almost any laptop with a built-in USB-C host cable & attached USB-C to USB-A dongle; Supports resolutions up to 4K 30Hz (HDMI 1.4, Video Output 1) & 1080p 60Hz (HDMI 1.2, Video Output 2)
- **APPLE M1/M2/M3 DUAL DISPLAY COMPATIBLE:** Universal compatibility with macOS, Windows and ChromeOS, enabling extended dual displays on USB & TB3/4 laptops incl. Apple M1/M2/M3 MacBooks which are not capable of driving more than 1 external display natively
- **HIGH-PERFORMANCE:** 3-Port USB Type-A (5Gbps) Hub for fast/reliable data transfer; Works with legacy USB 2.0/1.1; Portable bus-powered adapter; Silicon Motion's Content Adaptive Technology uses processing algorithms to reduce latency for smoother graphics
- **EXTRA-LONG CABLE:** Extended port reach with attached 1.3ft (40cm) host cable for easy setup that prevents adapter from dangling on the host connector; Ideal cable length to reduce port strain on 2-in-1 convertible laptops, or host laptops on riser stands
- **OUR ADVANTAGE:** Hybrid Mini docking station incl. Connectivity Tools app w/USB Event Monitoring to log/timestamp USB port usage for admins to identify potentially malicious devices & Windows Layout Utility restores app locations when re-connecting displays

---

### Hardware

Warranty	3 Years
4K Support	Yes

Fast-Charge Port(s)	No
Displays Supported	2
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB-C USB-A
Industry Standards	HDMI 1.4 HDMI 1.2 USB 3.2 Gen 1 (5Gbps)
Chipset ID	SMI - SM768G0 ITE - IT66121FN VIA - VL817C0 Terminus - FE1.1S

---

### Performance

Maximum Data Transfer Rate	5Gbps
Maximum Digital Resolutions	Video Output 1: 4K 30Hz Video Output 2: 1080p 60Hz
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
UASP Support	Yes
MTBF	30,000 Hours

---

### Connector(s)

External Ports	2 - HDMI (19 pin) 3 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)
Host Connectors	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps) 1 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)

---

### Software

OS Compatibility	Windows 7
------------------	-----------

Windows 8.1

Windows 10

Windows 11

macOS Mojave (10.14)

macOS Catalina (10.15)

macOS Big Sur (11.0)

macOS Monterey (12.0)

macOS Ventura (13.0)

macOS Sonoma (14.0)

ChromeOS

<i>Note: ChromeOS can only achieve dual 1080p when outputting video to two external monitors

---

**Special Notes / Requirements**

System and Cable Requirements

Manual driver installation is required for macOS

Note

USB 3.2 Gen 1 (5Gbps) is also known as USB 3.1 Gen 1 (5Gbps) and USB 3.0 (5Gbps)

---

**Power**

Power Source

Bus Powered

---

**Environmental**

Operating Temperature

0C to 40C (32F to 104F)

Storage Temperature

-10C to 60C (14F to 140F)

Humidity

10% to 90% RH

---

**Physical Characteristics**

Color

Space Gray

Material

Aluminum

Cable Length

15.7 in [40 cm]

Product Length

4.7 in [12.0 cm]

Product Width

2.2 in [5.7 cm]

Product Height	0.6 in [1.6 cm]
Weight of Product	4.0 oz [114.0 g]

---

**Packaging Information**

Package Length	7.1 in [18.0 cm]
Package Width	5.0 in [12.6 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	6.2 oz [177.0 g]

---

**What's in the Box**

Included in Package	1 - Multiport Adapter
	1 - Quick-Start Guide

---

*\*Product appearance and specifications are subject to change without notice.*