

## 1U 17" Rackmount LCD Console w/ Rear Mount KVM Switch Module

**Product ID:** 1UCABCONS17



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 17in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

## Certifications, Reports and Compatibility



## Applications

## Features

- A compact and efficient way to control multiple computers in a 19" by 36" deep Rack Cabinet.

- Comfortable laptop design with integrated keyboard and touchpad mouse
- Optional 8 or 16 port KVM switch modules lets users controls up to 16 computers directly, and up to 136 computers in total
- High resolution 17" Active Matrix Color TFT LCD monitor, displays up to 1280 x 1024 pixels
- Adjustable mounting brackets to fit any cabinet
- Standard 19" 1U rack drawer
- Drawer locks firmly into position firmly when in use
- Quick and easy installation

---

## Hardware

Warranty	2 Years
Front Door Key Lock	No
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Industry Standards	VESA DDC 1/2B, VESA DPMS compliant
Daisy-Chain	Yes

---

## Performance

DVI Support	No
IP Control	No
Maximum Analog Resolutions	1280 x 1024
Aspect Ratio	Standard (4:3)

Response Time	5ms
Contrast Ratio	1000:1
Brightness	350 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.264 x 0.264 mm
Viewing Angle	170 (H), 160 (V)
Maximum Number of Users	1
Port Selection Support	Push Button and OSD (On Screen Display)
MTBF	360,562 Hours

---

#### Connector(s)

Console Interface(s)	2 - PS/2 (6 pin, Mini-DIN)
	1 - VGA (15 pin, High Density D-Sub)

---

#### Special Notes / Requirements

Note	Power consumption for Standby, Suspend and Off modes is <= 1W
------	---

---

#### Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	1.8A
Output Voltage	12V DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	26.5W

---

#### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	20.7 in [52.5 cm]
Product Width	19.0 in [48.3 cm]
Product Height	15.0 in [38.1 cm]
Weight of Product	22.4 lb [10.2 kg]
Minimum Mounting Depth	30.1 in [76.5 cm]

---

#### Packaging Information

Package Length	27.7 in [70.3 cm]
Package Width	24.5 in [62.2 cm]
Package Height	11.3 in [28.8 cm]
Shipping (Package) Weight	41.0 lb [18.6 kg]

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***