

1U 19" Rackmount LCD Console w/ Rear Mount KVM Switch Module

Product ID: 1UCABCONS19



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 19in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

Certifications, Reports and Compatibility



Applications

- Managing cabinet-mounted servers
- Improving the internal space efficiency of existing cabinets
- Centralized control of dozens of PCs and servers if used with optional KVM modules.

Features

- Flip-open 19" TFT LCD panel supports 1280 x 1024@60/70/75Hz resolution
- Standard 19" 1U rack drawer
- Modular design
- Full 105 key, low-profile, sturdy keyboard built-in
- Standard connectors for PC connection
- Locking mechanism locks the drawer when pulled out, pushed in or folded down
- Supports replaceable keyboard, mouse and module selection
- Ergonomic hand rest design
- For rack cabinet with depth from 20" (50cm) and up (with appropriate Rear bracket & extension kit)
- Quick and easy installation

Hardware

Warranty	2 Years
Front Door Key Lock	No
Audio	No
Display Size	19in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes

Industry Standards	VESA DPMS compliant
Daisy-Chain	Yes

Performance

DVI Support	No
IP Control	No
Maximum Analog Resolutions	1280 x 1024 pixels
Aspect Ratio	Standard (4:3)
Response Time	8ms
Contrast Ratio	2000:1
Brightness	300 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.294 x 0.294 mm
Viewing Angle	178 (H), 178 (V)
MTBF	360,562 Hours

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	1.8A
Output Voltage	12V DC
Output Current	4A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	28W

Environmental

Operating Temperature	0 to +50
Storage Temperature	-20 to +60

Physical Characteristics

Color	Black
-------	-------

Packaging Information

Package Length	24.8 in [63 cm]
Package Width	31.5 in [80 cm]
Package Height	10.7 in [27.2 cm]
Shipping (Package) Weight	45.4 lb [20.6 kg]

What's in the Box

Included in Package	1 - 19in Rack Console
	1 - 1 Port Rear Mount KVM Module
	2 - Mounting Brackets
	2 - Rear Bracket Extensions
	1 - Bag, Screws
	1 - Power Adapter (w/ Cord)
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***