

20-Outlet Rackmount PDU, 1U Server Power Strip, 16x C13 + 4x C19, 8x Front and 12x Rear Outlets, NEMA L6-30P Wall Connection, 30A/240V, UL-Listed, TAA

Product ID: 2030B8H-RACK-PDU-IC



Deliver consistent power to critical equipment in server rooms, AV racks, and test benches. This 1U 20-port rackmount PDU features IEC C13 and IEC C19 outlets, built-in circuit breakers, and versatile mounting options, making it a dependable power backbone for critical deployments.

Designed for dense IT and AV environments, this unit powers up to 20 devices through 16 IEC C13 outlets (4x front / 12x rear) and 4x IEC C19 outlets (front). The built-in 8ft (2.4m) power cord provides the flexibility and reach needed to accommodate various configurations.

User-resettable 15A breakers safeguard each IEC C19 outlet individually and every group of four IEC C13 outlets. If the total current draw exceeds safe operating limits, the integrated circuit breakers automatically cut power to prevent damage to the equipment.

Power delivery unit is TAA-compliant and includes 4-way mounting brackets that provide flexibility for horizontal or vertical mounting. The PDU is compatible with standard 19" EIA-310 racks that are at least 4in (10.1cm) deep and is constructed from durable, powder-coated SPCC steel for long-term reliability. Additionally, the built-in 8ft (2.4m) power cord provides the flexibility and reach needed to accommodate various configurations.

Certifications, Reports and Compatibility



Applications

Features

- **Centralized Rack Power**: This rack mounted power distribution unit delivers reliable 240V power for up to 20 devices, ideal for small to mid-sized IT environments, offices, and businesses needing an organized and efficient distribution system
- **Maximize Connection Flexibility**: Features 16 IEC C13 outlets (4x front / 12x rear) and 4x front facing IEC C19 outlets with individual circuit breakers; 8ft (2.4m) power cord with a NEMA L6-30P plug makes it easy to reach distant AC outlets
- **Mount Where You Need It**: TAA-compliant 1U PDU fits EIA-310 19" racks or cabinets over 4in (10.1cm) deep, or mounts on walls and desks (top/under) with included brackets; Rugged SPCC steel housing with powder-coated finish ensures long-term durability
- **Protect Equipment with Circuit Breaker**: User-resettable 15A breakers safeguard each IEC C19 outlet individually and every group of four IEC C13 outlets, helping prevent overloads and protect connected devices
- **The IT Pro's Choice**: Our rack-mount PDUs are lab-tested to ensure enterprise-grade reliability for continuous uptime and optimal performance in edge, on-prem, AV racks, and data center deployments; Backed by free lifetime 24/5 technical assistance

Hardware

Warranty	2 Years
U Height	1U
Form Factor	Horizontal
Number of Power Outlets	12
Rack-Mountable	Yes
Industry Standards	UL 1363 EIA/ECA-310-E

Performance

Maximum Total Current	30A
Maximum Total Current Draw per Phase	30A
Regulatory Derated Input Current (North America)	24A
Nominal Input Voltage	200V - 240V
Nominal Output Voltage	200V - 240V
Maximum Output Voltage	200V - 240V

Connector(s)

Input Connector(s)	1 - NEMA L6-30P Power (North America)
Output Connectors	16 - IEC 60320 C13 Power 4 - IEC 60320 C19 Power

Power

Input Voltage	240V AC
Plug Type	IEC 60320 C13 Power IEC 60320 C19 Power

Physical Characteristics

Color	Black
Material	Steel
Cable Length	7.9 ft [2.4 m]
Product Length	1.5 ft [0.5 m]
Product Width	3.7 in [95.2 mm]
Product Height	1.7 in [43.3 mm]
Weight of Product	117.9 oz [3339 g]

Packaging Information

Package Length	11.1 in [28.1 cm]
Package Width	20.1 in [51.1 cm]
Package Height	3.0 in [7.6 cm]
Shipping (Package) Weight	8.0 lb [3.6 kg]

What's in the Box

Included in Package	1 - Rack-Mount PDU 4 - M5 Cage Nuts 4 - M5x12mm Rack Screws
---------------------	---

4 - Middle Washer

4 - Plastic Washer

1 - Product Documentation

**Warranty
Information**

Warranty

2 Years

**Product appearance and specifications are subject to change without notice.*