

10ft (3m) Power Extension Cord, NEMA 5-15P to NEMA 5-15R AC Power Cable, 10A 125V, 18AWG, Outlet Extension Power Cable, AC Power Cord, TAA Compliant, UL Listed

Produkt-ID: 231A-8A00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend a monitor, scanner, printer, or PC power cord by an additional 10 ft
- Extend a power connection from a crowded PDU for more convenient access

Merkmale

- **POWER EXTENSION CORD:** 10ft (3m) 18AWG Universal Power Extension Cord with NEMA 5-15P to NEMA 5-15R connector is suitable for workstations/home office; Indoor use; Rated to carry 125V at 10A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 10ft (3m); TAA Compliant; NEMA 5-15P to NEMA 5-15R; 18AWG; 125V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.31in (7.8mm)
- **COMPATIBILITY:** Extend the length of a power cord from your desktop computer, server, or printer to a wall outlet or PDU; NEMA 5-15P plug works with North American electrical outlets; Replacement AC power extension cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This 5-15P to 5-15R power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Typ der PVC
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1
e

Kabeltyp SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung	125V AC
Eingangsstrom	10A

Umgebungsbedingungen

Betriebstemperatur	-20° to 105°C (-4° to 221°F)
Lagertemperatur	-20° to 105°C (-4° to 221°F)
Feuchtigkeit	0% to 65% RH

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	10.0 ft [3.0 m]
Außendurchmesser des Kabels	0.3 in [7.8 mm]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.1 in [2.7 cm]
Produkthöhe	1.4 in [3.5 cm]
Produktgewicht	11.4 oz [324.0 g]

Verpackungsinformationen

Paketlänge	10.8 in [27.4 cm]
Paketbreite	5.4 in [13.7 cm]
Pakethöhe	1.6 in [4.0 cm]

Versandgewicht 11.8 oz [334.0 g]
(Verpackung)

Verpackungsinhalt

Im Paket enthalten 1 - 3m NEMA 5-15P auf NEMA 5-15R Netzkabel

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

