

15U Rack Enclosure Server Cabinet - 29 in. Deep - Built-in Fans

Product ID: 2636CABINET



This 15U, 36 in (depth) cabinet features a plexiglass front door, full steel design, and three-fan filtered ventilation helping to keep your servers and other critical equipment cool and protected. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server equipment cabinet/rack is black, making an attractive addition to your server room, and to ensure maximum versatility, the rack/cabinet includes casters, making it easier to position server equipment as needed.

Certifications, Reports and Compatibility

Applications

Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable mounting rails inside cabinet
- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled

- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	15U
Special Features	Adjustable Mounting Rails
	Built-in Cable Management
	Leveling Feet
	Ships Fully Assembled
	Casters (Included)
Mounting Rail Profile	L-Shape
Fan Options	Three Fans Included: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Airflow Rate	82 CFM
Audible Noise	38 dBA @ 1 Meter
Weight Capacity (Stationary)	2210.0 lb [1000 kg]

Physical Characteristics

Color	Black
-------	-------



Front Door Construction	Steel with Glass Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Rear Door Construction	Steel
Rear Door Features	Secure Key Lock with Reversible and Removable Back Door

Product Measurements

Internal Width	21.9 in [55.6 cm]
Internal Depth	33.9 in [86 cm]
Product Length	35.4 in [90 cm]
Product Width	22.0 in [55.9 cm]
Product Height	30.1 in [76.5 cm]
Weight of Product	136.3 lb [61.7 kg]
Maximum Mounting Depth	29.3 in [74.5 cm]
Minimum Mounting Depth	13.4 in [34 cm]
Product Height with Casters	33.2 in [84.3 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	36.1 in [91.8 cm]
Package Width	23.3 in [59.3 cm]
Package Height	39.3 in [99.7 cm]
Shipping (Package) Weight	144.4 lb [65.3 kg]

What's in the Box

Included in Package	Cabinet Equipment Rack
---------------------	------------------------



M5 Screws

Sets of Keys

M5 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

