

8ft (2.4m) Computer Power Cord, NEMA 5-15P to C13 AC Power Cable, 13A 125V, 16AWG, Monitor Power Cable, PC Power Supply Cable, TAA Compliant, UL Listed

Produkt-ID: 271B-6800-POWER-CORD



#### The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Connect a computer, display, or laptop power supply to a wall outlet or PDU

## Merkmale

- AC POWER CORD: 8ft (2.43m) 16AWG Universal Power Cord with NEMA 5-15P to IEC 60320 C13 connector is suitable for workstations/home office; Indoor use; Rated to carry 125V at 13A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 8ft (2.43m); TAA Compliant; NEMA 5-15P to IEC 60320 C13; 16AWG; 125V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: NEMA 5-15P plug works with North American electrical outlets; IEC C13 connector works with most computers, monitors, and displays; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This 5-15P to C13 power cord is available in other lengths

---

### Hardware

#### Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Typ der PVC  
Kabelummantelung

Feuerwiderstandsklass Klasse VW-1  
e

Kabeltyp SJT

---

### Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)

Steckverbinder B 1 - IEC 60320 C13 Strom

---

Strom

Eingangsspannung 125V AC

Eingangsstrom 13A

---

Umgebungsbedingungen

Betriebstemperatur -20° to 105°C (-4° to 221°F)

Lagertemperatur -20° to 105°C (-4° to 221°F)

Feuchtigkeit 0% to 65% RH

---

Physische Eigenschaften

Farbe Schwarz

Drahtstärke 16 AWG

Kabellänge 8.0 ft [2.4 m]

Außendurchmesser des Kabels 0.3 in [8.5 mm]

Produktlänge 8.0 ft [2.4 m]

Produktbreite 1.0 in [2.6 cm]

Produkthöhe 1.0 in [2.6 cm]

Produktgewicht 11.0 oz [312.0 g]

---

Verpackungsinformationen

Paketlänge 8.9 in [22.5 cm]

Paketbreite 3.6 in [9.2 cm]

Pakethöhe 2.3 in [5.9 cm]

Versandgewicht (Verpackung) 11.2 oz [318.0 g]

---

Verpackungsinhalt

Im Paket enthalten 1 - 2,4m NEMA 5-15P auf C13 Netzkabel

---

Garantieinformationen

Warranty Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.

