

8ft (2.4m) Computer Power Cord, NEMA 5-15P to C13 AC Power Cable, 13A 125V, 16AWG, Monitor Power Cable, PC Power Supply Cable, TAA Compliant, UL Listed

Product ID: 271B-6800-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility











Applications

• Connect a computer, display, or laptop power supply to a wall outlet or PDU

Features

- AC POWER CORD: 8ft (2.43m) 16AWG Universal Power Cord with NEMA 5-15P to IEC 60320 C13 connector is suitable for workstations/home office; Indoor use; Rated to carry 125V at 13A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 8ft (2.43m); TAA Compliant; NEMA 5-15P to IEC 60320 C13; 16AWG; 125V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: NEMA 5-15P plug works with North American electrical outlets; IEC C13 connector works with most computers, monitors, and displays; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This 5-15P to C13 power cord is available in other lengths

Hardware		
	Warranty	Lifetime
	Number of Conductors	3
	Cable Jacket Material	PVC
	Fire Rating	VW-1 Rated
	Cable Type	SJT
Connector(s)		
	Connector A	1 - NEMA 5-15 Power (North America)
	Connector B	1 - IEC 60320 C13 Power
Power		
	Input Voltage	125V AC
	Input Current	13A





Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Black
	Wire Gauge	16 AWG
	Cable Length	8.0 ft [2.4 m]
	Cable OD	0.3 in [8.5 mm]
	Product Length	8.0 ft [2.4 m]
	Product Width	1.0 in [2.6 cm]
	Product Height	1.0 in [2.6 cm]
	Weight of Product	0.0 oz [0.0 g]
Packaging Information		
	Package Length	5.7 in [14.5 cm]
	Package Width	11.6 in [29.5 cm]
	Package Height	2.8 in [7.0 cm]
	Shipping (Package) Weight	11.2 oz [318.0 g]
What's in the Box		
	Included in Package	1 - 8ft NEMA 5-15P to C13 Power Cord

^{*}Product appearance and specifications are subject to change without notice.