

12ft (3.6m) Heavy Duty Power Cord, NEMA 5-15P to Locking C13 AC Power Cable, 15A 125V, 14AWG, Replacement Computer Power Cord, TAA Compliant, UL Listed

Product ID: 27LC-4B00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Locking C13 connector hinders accidental power disconnection
- Connect a computer, display, or laptop power supply to a wall outlet or PDU

Features

- **HEAVY DUTY AC POWER CORD:** 12ft (3.66m) 14AWG Universal Power Cord with NEMA 5-15P to Locking IEC 60320 C13 connector is suitable for workstations/home office or high-power rack mounted equipment such as servers and PDUs; Indoor use; Up to 125V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 12ft (3.66m); TAA Compliant; NEMA 5-15P to Locking IEC 60320 C13; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA 5-15P plug works with North American electrical outlets; IEC C13 connector works with most computers, monitors, and displays; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Performance

Maximum Cable Length	12.0 ft [3.7 m]
----------------------	-----------------

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Power

Input Voltage	125 AC
Input Current	15A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	14 AWG
Cable Length	12.0 ft [3.7 m]
Cable OD	0.4 in [9.3 mm]
Product Length	12.0 ft [3.7 m]
Product Width	1.2 in [2.9 cm]
Product Height	1.0 in [2.6 cm]
Weight of Product	1.2 lb [0.6 kg]

Packaging Information

Package Length	5.5 in [14.0 cm]
Package Width	15.6 in [39.5 cm]
Package Height	3.5 in [9.0 cm]
Shipping (Package) Weight	1.3 lb [0.6 kg]

What's in the Box

Included in Package 1 - 12ft NEMA 5-15P to Locking C13 Power Cord

****Product appearance and specifications are subject to change without notice.***