

42U 2 Post Open Frame Rack with Casters

Product ID: 2POSTRACK



This 42U 2 Post Open Frame Rack offers full steel construction instead of the aluminum used in competitive products, providing greater durability and stability that reduces the need for concrete mounting kits.

A cost-effective solution for mounting network equipment and telecom equipment, this two post rack features square mounting holes on the frame that allow you to easily mount ANSI/EIA RS-310-D compliant network equipment without additional hardware.

Easy to deploy, the two post open frame rack can be assembled in minutes and is backed by StarTech.com's Lifetime Warranty - ensuring a permanent server/telecom storage solution.

Certifications, Reports and Compatibility

Applications

- Server rooms or other locations where telecomm and networking equipment need to be housed

Features

- Flat-packed design reduces handling costs
- Easy assembly at the point of installation for rapid deployment
- Full steel construction for superior durability and stability
- Mount standard networking equipment using standard cage nuts and screws

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	2-Post
Frame Type	Steel
U Height	42U
Fan(s)	No
Casters	Included
Industry Standards	EIA RS310-D
	IEC297-2
	GB/T3047.2-92
	DIN41491 Part I
	DIN41491 Part VII

Performance

Weight Capacity (Stationary)	331.5 lb [150 kg]
------------------------------	-------------------

Physical Characteristics

Color	Black
Internal Width	18.3 in [46.5 cm]
Weight of Product	50.2 lb [22.7 kg]
Product Height with Casters	6.8 ft [2.1 m]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	6.5 ft [2.0 m]
Package Width	5.9 in [15 cm]



Package Height	6.5 in [16.5 cm]
Shipping (Package) Weight	54.1 lb [24.5 kg]

****Product appearance and specifications are subject to change without notice.***

