

## USB 3.0 Internal Multi-Card Reader with UHS-II Support - TAA

**Product ID:** 35FCREADBU3



Now, you can transfer large files like photos and 4K video, back up files or offload data, to and from your memory cards, at speeds like never before. This USB 3.0 internal multi-card reader supports UHS-II to greatly enhance your file transfer rates. The card reader supports High Capacity/eXtended Capacity cards and most standard memory cards, including SecureDigital, Compact Flash, Memory Stick and micro SD cards. It also enables concurrent downloads. Fast speed and wide compatibility make this multi-card reader an ideal solution for photo kiosks or photo labs, and desktop computers.

The card reader is USB powered so there's no external power or battery required. Front USB access lets you connect USB devices easily.

With support of UHS-II cards, the multi-card reader lets you transfer large files to and from your memory cards at speeds of up to 312 MB/s, saving you time on data offloads of 4K, full HD and 3D videos.

Using a USB 3.0 connection, also known as USB 3.1 Gen 1, the card reader supports fast file transfer speeds of up to 5 Gbps, enabling you to leverage the increased capabilities of new, higher performing memory cards.

Save time with concurrent downloads. This 5-slot multi-card reader design allows you to access up to four memory cards simultaneously for fast and easy file transfers.

The USB 3.0 multi-card reader works with most standard memory cards, including:

- Secure Digital (Standard Card, HC card, XC card, MMC, Mini SD with adapter)
- Micro SD (Standard card, HC card, XC card)
- Compact Flash (CF I or II, CF 6.0)
- Memory Stick (Standard, Pro, Duo, Pro Duo, Pro-HG, XC, Micro MS with adapter)

The 35FCREADBU3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Provide read/write access to a wide range of memory cards, ideal for photo labs and kiosks
- Read and copy high-res image files quickly and efficiently, an effective solution for medical units, school systems and business applications
- Back-up and copy data, photos and video from your memory cards to your home computer, or from your computer to a memory card

## Features

- **USB 3.0 MULTI-CARD READER:** This Internal USB 3.0 Multi-Card Reader fits into any 3.5in drive bay and connects internally to a 20-pin motherboard header; Access the most popular flash card formats from a desktop computer; 20-pin IDC cable and screws incl.
- **WIDE COMPATIBILITY:** Supports CompactFlash type I, SD/miniSD/microSD/SDHC/SDXC, MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC, MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture card; Front facing USB 3.0 port
- **SIMULTANEOUS SLOT ACCESS:** This internal multi-card reader supports access to four different card slots simultaneously (excluding same type media), allowing you to conveniently copy files from or between different media cards at the same time
- **CONVENIENT SETUP:** OS independent supporting Windows, macOS, and Linux; Built-in Power and Activity LEDs; Ideal for saving, editing & transferring content in videography, photography, podcasting, YouTube & social media
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this TAA compliant internal multi-card reader is backed for 2 years, including free lifetime 24/5 multi-lingual assistance

---

### Hardware

Warranty	2 Years
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB 3.2 Gen 1 (5Gbps)

Number of Drives	2
Chipset ID	Realtek - RTS5321

## Performance

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
	SDXC (Secure Digital eXtended Capacity)
	SDHC (Secure Digital High Capacity)
	Mini-SD, Micro-SD (Mini/Micro Secure Digital)
	microSDHC (Micro Secure Digital High Capacity)
	CF (Compact Flash I/II Card)
	HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)
	MS/MS Pro (Memory Stick/Memory Stick Pro)
	MS Duo, MS Pro Duo, MS Pro-HG Duo
	MSXC (Memory Stick eXtended Capacity)
	HS-MS (High Speed Memory Stick)
	MS Micro (Memory Stick Micro)
	MS MG (Memory Stick w/ MagicGate)

## Connector(s)

Drive Connectors	2 - SD / MMC Slot
	1 - Memory Stick / Memory Stick Pro Slot
	1 - MicroSD
	1 - CompactFlash (50 pin) Slot
	1 - USB 3.2 Type-A (9 pin, Fast-Charge)
Host Connectors	1 - IDC (20 pin, USB 3.0, Motherboard Header)

## Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

## Indicators

LED Indicators	2 - Power and Access
----------------	----------------------

## Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	15% ~ 85% RH

## Physical Characteristics

Color	Black
Material	Steel and Plastic
Cable Length	16.1 in [41 cm]
Product Length	4.6 in [11.8 cm]
Product Width	3.9 in [10 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	8.8 oz [250 g]

## Packaging Information

Package Quantity	1
Package Length	6.4 in [16.2 cm]
Package Width	5.5 in [14.0 cm]
Package Height	1.7 in [4.2 cm]
Shipping (Package) Weight	11.0 oz [312 g]

## What's in the Box

Included in Package	1 - USB 3.0 memory card reader
	4 - mounting screws
	1 - quick start guide

---

***\*Product appearance and specifications are subject to change without notice.***