

15 ft Cat5e Orange Snagless Crossover RJ45 UTP Cat5e Patch Cable 15ft Patch Cord

Product ID: 45CROSS15OR



StarTech.com's 15 ft (Orange) Cat 5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials (100% Copper core, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connects workstation to workstation
- Patches from hub to hub

Features

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- Clip protector keeps the plug from snagging while routing the cable

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated
Cable Type	Crossover Snag-less

Performance

Cable Rating	CAT5e - 350 MHz
--------------	-----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Orange
Wire Gauge	24 AWG
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.9 in [24 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	6.0 oz [170 g]

What's in the Box

Included in Package	15 Ft Orange Cat 5E Cross Patch Cable
---------------------	---------------------------------------

**Product appearance and specifications are subject to change without notice.*

