

3 ft Cat5e Yellow Snagless Crossover RJ45 UTP Cat5e Patch Cable 3ft Patch Cord

Product ID: 45CROSS3YL



StarTech.com's 3 ft (Yellow) Cat 5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials (100% Copper core, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connects workstation to workstation
- Patches from hub to hub

Features

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- Clip protector keeps the plug from snagging while routing the cable

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated
Cable Type	Crossover Snag-less

Performance

Cable Rating	CAT5e - 350 MHz
Maximum Cable Length	328.0 ft [100 m]

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Yellow
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.4 in [11 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	3 Ft. Yellow Cat. 5E Cross Patch Cable
---------------------	--



****Product appearance and specifications are subject to change without notice.***

