

6 ft Cat5e Gray Snagless Crossover RJ45 UTP Cat5e Patch Cable 6ft Patch Cord

Product ID: 45CROSS6GR



StarTech.com's 6ft (Gray) Cat 5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials (100% Copper core, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connects workstation to workstation
- Patches from hub to hub

Features

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits

- Clip protector keeps the plug from snagging while routing the cable

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated
Cable Type	Crossover Snag-less

Performance

Cable Rating	CAT5e - 350 MHz
--------------	-----------------

Connector(s)

Connector A	1 - RJ-45
Connector B	1 - RJ-45

Physical Characteristics

Color	Gray
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.0 in [0 cm]
Product Height	0.0 in [0 cm]
Weight of Product	0.0 oz [0 g]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	0.6 in [14 mm]
Package Height	8.3 in [21.1 cm]

Shipping (Package) Weight	0.2 lb [0.1 kg]
------------------------------	-----------------

What's in the Box

Included in Package	1 - 6 Ft. Gray Cross Wired RJ45 Patch Cable
---------------------	---

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*