

Cat5e Patch Cable with Snagless RJ45 Connectors - 3 ft, Black

Produkt-ID: 45PATCH3BK



The 45PATCH3BK Cat5e Patch Cable (3 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This RJ45 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Merkmale

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 Pair UTP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CM e

Leistung

Kabelnennwerte	CAT5e - 100 MHz
----------------	-----------------

Steckverbinder

Steckverbinder A	1 - RJ-45
------------------	-----------

Steckverbinder B		1 - RJ-45
Physische Eigenschaften		
	Farbe	Schwarz
	Drahtstärke	24 AWG
	Leitungstyp	Feindrähtiges Kupfer
	Kabellänge	3.0 ft [0.9 m]
	Produktlänge	3.0 ft [0.9 m]
	Produktbreite	0.5 in [1.2 cm]
	Produkthöhe	0.5 in [1.4 cm]
	Produktgewicht	1.3 oz [37.0 g]
Verpackungsinformationen		
	Paketmenge	1
	Paketlänge	7.0 in [17.7 cm]
	Paketbreite	7.8 in [19.9 cm]
	Pakethöhe	0.9 in [2.4 cm]
	Versandgewicht (Verpackung)	1.0 oz [28.0 g]
Verpackungsinhalt		
	Im Paket enthalten	1 - 3ft Black RJ45 Cat5e Patch Cable
Garantieinformationen		
	Warranty	Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.