


## Cat5e Patch Cable with Snagless RJ45 Connectors - 50 ft, Red

Produkt-ID: 45PATCH50RD



The 45PATCH50RD Cat5e Patch Cable (50 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable red PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This RJ45 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Ethernet network devices by 50

## Merkmale

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

---

### Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 4 pair UTP

Typ der PVC - Polyvinyl Chloride  
Kabelummantelung

Feuerwiderstandsklass Ausgelegt gemäß CM  
e

---

### Leistung

Kabelnennwerte CAT5e - 100 MHz

---

Steckverbinder

Steckverbinder A 1 - RJ-45

Steckverbinder B 1 - RJ-45

---

Physische  
Eigenschaften

Farbe	Rot
Drahtstärke	24 AWG
Leitungstyp	Feindrähtiges Kupfer
Kabellänge	50.0 ft [15.2 m]
Produktlänge	50.0 ft [15.2 m]
Produktbreite	0.4 in [1.1 cm]
Produkthöhe	1.8 in [4.7 cm]
Produktgewicht	1.0 lb [0.5 kg]

---

Verpackungsinform  
ationen

Paketmenge	1
Paketlänge	8.3 in [21.2 cm]
Paketbreite	8.6 in [21.9 cm]
Pakethöhe	1.6 in [4.0 cm]
Versandgewicht (Verpackung)	1.2 lb [0.6 kg]

---

Verpackungsinhalt

Im Paket enthalten 1 - 50ft Red RJ45 Cat5e Patch Cable

---

Garantieinformatio  
nen

Warranty Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.