

## Caster Kit for Open Frame Rack - 4POSTRACK

Product ID: 4POSTCASTER



This set of four casters allow you to move and adjust the position of your rack to suit your needs. The casters connect to the bottom of any rack with 42 mm x 55 mm caster mounting holes such as our:

- 12U Adjustable 4-Post Rack (4POSTRACK12)
- 25U Adjustable 4-Post Rack (4POSTRACK25)
- 36U Adjustable 4-Post Rack (4POSTRACK36)
- 42U Adjustable 4-Post Rack (4POSTRACKBK)
- 12U Rack Enclosure Server Cabinet (RKQMCAB12)

This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

4POSTCASTER is backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

### Features

- Max load capacity of 50 kg (110 lbs) per caster, total of 200 kg (440 lbs)
- Includes all hardware required for installation
- TAA compliant for GSA Schedule purchases

---

Performance	Warranty	Lifetime
	Weight Capacity per Caster (Stationary)	220.0 lb [99.5 kg]
		110.0 lb [49.8 kg]

Weight Capacity per  
Caster (Rolling)

<b>Physical Characteristics</b>	Product Height	3.4 in [87 mm]
	Weight of Product	3.6 lb [1.6 kg]
<b>Packaging Information</b>	Package Length	3.7 in [95 mm]
	Package Width	3.3 in [84 mm]
	Package Height	1.5 in [39 mm]
	Shipping (Package) Weight	4.0 lb [1.8 kg]
<b>What's in the Box</b>	Included in Package	Casters
	Included in Package	Mounting Screws

*\*Product appearance and specifications are subject to change without notice.*

