

12U 4 Post Server Equipment Open Frame Rack Cabinet w/ Adjustable Posts & Casters

Product ID: 4POSTRACK12A



The 4POSTRACK12A Open Frame Rack offers a durable, yet flexible open-air housing for rack-mount servers and networking equipment. The rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform with two adjustable posts for variable mounting depths. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Providing a universal design that's compatible with equipment from popular manufacturers, this EIA-RS-310C compliant open rack ships flat packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, this 12U rack ships with 4 swiveling casters and has a total height of less than 26" (661mm) which allows the rack to be rolled under most desks or work benches with little effort.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Useful for point of sale applications, specifically mounting equipment under the check-out counter
- Suitable for rackmount equipment where security at the rack level is not required
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Mounting equipment under a desk/workspace

- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- 12U open frame design for easy access and greater air flow
- Swivel Casters included
- TAA compliant for GSA Schedule purchases
- Two adjustable rails for variable mounting depths
- Shipped as a flat-pack for easier handling
- Less than 3ft tall, perfect for rolling under desks or benches
- Heavy gauge mounting rails


Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Casters (Included)
	Easy Assembly
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	596.7 lb [270 kg]
------------------------------	-------------------

Physical Characteristics



Color	Black
Construction Material	Steel

Product Measurements

Product Length	35.9 in [91.3 cm]
Product Width	21.0 in [53.4 cm]
Product Height	23.1 in [58.6 cm]
Weight of Product	34.5 lb [15.6 kg]
Maximum Mounting Depth	35.9 in [91.3 cm]
Minimum Mounting Depth	3.8 in [97 mm]
Product Height with Casters	25.9 in [65.7 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	36.3 in [92.1 cm]
Package Width	24.4 in [62.0 cm]
Package Height	6.5 in [16.4 cm]
Shipping (Package) Weight	41.1 lb [18.6 kg]

What's in the Box

Included in Package	Front/Rear Frame
	Assembly Post
	Adjustable Rails
	Casters
	1/4-20 x 12 Hex Bolts
	1/4" Washers



KEP Nuts

M6 Screws

M6 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

