

## 12U 4 Post Server Equipment Open Frame Rack Cabinet w/ Adjustable Posts & Casters

**Product ID:** 4POSTRACK12A



The 4POSTRACK12A Open Frame Rack offers a durable, yet flexible open-air housing for rack-mount servers and networking equipment. The rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform with two adjustable posts for variable mounting depths. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Providing a universal design that's compatible with equipment from popular manufacturers, this EIA-RS-310C compliant open rack ships flat packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, this 12U rack ships with 4 swiveling casters and has a total height of less than 26" (661mm) which allows the rack to be rolled under most desks or work benches with little effort.

Backed by a StarTech.com Lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Useful for point of sale applications, specifically mounting equipment under the check-out counter
- Suitable for rackmount equipment where security at the rack level is not required

- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Mounting equipment under a desk/workspace
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

## Features

- 12U open frame design for easy access and greater air flow
- Swivel Casters included
- TAA compliant for GSA Schedule purchases
- Two adjustable rails for variable mounting depths
- Shipped as a flat-pack for easier handling
- Less than 3ft tall, perfect for rolling under desks or benches
- Heavy gauge mounting rails

## Hardware

|                       |                           |
|-----------------------|---------------------------|
| Warranty              | Lifetime                  |
| Wallmountable         | No                        |
| Rack Type             | 4-Post                    |
| Frame Type            | Open Frame                |
| U Height              | 12U                       |
| Special Features      | Adjustable Mounting Rails |
|                       | Castors (Included)        |
|                       | Easy Assembly             |
| Mounting Rail Profile | L-Shape                   |
| Mounting Hole Types   | Square (For Cage Nut)     |
| Industry Standards    | EIA/ECA-310-E             |

## Performance

|                                 |                   |
|---------------------------------|-------------------|
| Weight Capacity<br>(Stationary) | 595.4 lb [270 kg] |
|---------------------------------|-------------------|

---

**Physical Characteristics**

|                       |       |
|-----------------------|-------|
| Color                 | Black |
| Construction Material | Steel |

---

**Product Measurements**

|                             |                   |
|-----------------------------|-------------------|
| Product Length              | 35.9 in [91.3 cm] |
| Product Width               | 21.0 in [53.4 cm] |
| Product Height              | 23.1 in [58.6 cm] |
| Weight of Product           | 34.4 lb [15.6 kg] |
| Maximum Mounting Depth      | 35.9 in [91.3 cm] |
| Minimum Mounting Depth      | 3.8 in [9.7 cm]   |
| Product Height with Casters | 25.9 in [65.7 cm] |

---

**Packaging Information**

|                               |                   |
|-------------------------------|-------------------|
| Flat Pack (Assembly Required) | Yes               |
| Package Length                | 36.5 in [92.8 cm] |
| Package Width                 | 24.6 in [62.5 cm] |
| Package Height                | 6.3 in [16.1 cm]  |
| Shipping (Package) Weight     | 40.8 lb [18.5 kg] |

---

**What's in the Box**

|                     |                            |
|---------------------|----------------------------|
| Included in Package | 2 - Front/Rear Frame       |
|                     | 4 - Assembly Post          |
|                     | 2 - Adjustable Rails       |
|                     | 4 - Casters                |
|                     | 52 - 1/4-20 x 12 Hex Bolts |

52 - 1/4" Washers

16 - KEP Nuts

16 - M6 Screws

16 - M6 Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***