

4-Post 12U Mobile Open Frame Server Rack, Four Post 19" Network Rack with Wheels, Rolling Rack with Adjustable Depth for Computer/AV/Data/IT Equipment - Casters, Leveling Feet or Floor Mounting

**Product ID:** 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 40494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

## Certifications, Reports and Compatibility



## Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required

- Rack-mounting A/V equipment in a radio or television studio

## Features

- **ADJUSTABLE DEPTH:** 4- Post 12U open frame server rack with 4 vertical rails and adjustable mounting depth 22" to 40" (56,0cm to 101,7cm); Compatible with various servers / switches / data / AV and other IT equipment; EIA/ECA-310-E Compliant
- **EASY ASSEMBLY:** Mobile network rack with easy-to-follow assembly instructions and online video; Compact flat-pack shipping to avoid damage and facilitate installation; Only 25in (64cm) high, ideal for utility/server closets or narrow home/office spaces
- **COLD ROLLED STEEL:** Durable 4 Post 19" open frame rack designed for ventilation with 12U mounting height and 1200lb (544kg) weight capacity (stationary); 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling computer/data rack includes cage nuts and screws to mount equipment, easy to read Units (U) and depth adjustment markings, cable management hooks for organization, and required assembly tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 12U rack is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Casters (Included)
	Easy Assembly
	Grounding Lug(s)
	Leveling Feet
	U-Markings

Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity (Stationary)	1199.5 lb [544 kg]
------------------------------	--------------------

---

#### Physical Characteristics

Color	Black
Construction Material	Steel

---

#### Product Measurements

Product Length	3.7 ft [1.1 m]
Product Width	23.6 in [60.0 cm]
Product Height	25.1 in [63.8 cm]
Weight of Product	50.1 lb [22.7 kg]
Maximum Mounting Depth	40.0 in [101.7 cm]
Minimum Mounting Depth	22.0 in [56 cm]
Product Height with Casters	28.0 in [71 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	14.2 in [36.1 cm]
Package Width	26.1 in [66.4 cm]
Package Height	6.0 in [15.3 cm]
Shipping (Package) Weight	56.0 lb [25.4 kg]

---

#### What's in the Box

Included in Package	2 - Left Vertical Rail
	2 - Right Vertical Rail
	2 - Base Bracket
	8 - Corner Section
	4 - Center Section
	2 - Top Bracket
	48 - M8 Bolt
	48 - M8 Washer
	1 - M8 (13mm) Wrench
	1 - M6 (10mm) Wrench
	1 - Phillips Screwdriver
	24 - M6 Cage Nut
	24 - PVC Cup Washer
	24 - M6 Phillips Head Screw
	4 - Cable Management Hook
	4 - Hook Mounting Screw
	4 - Casters
	4 - Leveling Feet
	16 - M6 Screw
	16 - M6 Flat Washer
	16 - M6 Flange Nut
	4 - Grounding Wires

---

***\*Product appearance and specifications are subject to change without notice.***