

12U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

Features

- 12U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Grounding Lug(s)
	Leveling Feet
	U-Markings
	Easy Assembly
	Casters (Included)
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	19.2 oz [544 g]
------------------------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	3.4 ft [1.0 m]
Product Width	23.8 in [60.4 cm]
Product Height	25.1 in [63.8 cm]
Weight of Product	50.3 lb [22.7 kg]
Maximum Mounting Depth	3.3 ft [1.0 m]
Minimum Mounting Depth	22.0 in [56 cm]
Product Height with Casters	28.0 in [71 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	25.6 in [65.0 cm]
Package Width	14.2 in [36.1 cm]
Package Height	6.3 in [16.0 cm]
Shipping (Package) Weight	58.2 lb [26.3 kg]

What's in the Box

Included in Package	Left Vertical Rail
	Right Vertical Rail



Base Bracket
Corner Section
Center Section
Top Bracket
M8 Bolt
M8 Washer
M8 (13mm) Wrench
M6 (10mm) Wrench
Phillips Screwdriver
M6 Cage Nut
PVC Cup Washer
M6 Phillips Head Screw
Cable Management Hook
Hook Mounting Screw
Casters
Leveling Feet
M6 Screw
M6 Flat Washer
M6 Flange Nut
Grounding Wires

****Product appearance and specifications are subject to change without notice.***

