

15U 19" Open Frame Server Rack - 4 Post Adjustable Depth 22-40" Mobile - Free Standing Rolling Network/Computer Equipment Data Rack - Dell PowerEdge HP ProLiant ThinkServer

Product ID: 4POSTRACK15U



The 15U open frame rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 15U 4 post rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40 in.) that make it easy to adapt the adjustable server rack to fit your equipment.

This durable free standing server rack supports a static loading capacity of up to 1220 lb. (544 kg) and portable rolling weight capacity of 660 lb. (300 kg). The rack also features offers compliance with the EIA/ECA-310 standard for a universal design that's compatible with most network equipment rack equipment.

For a complete server storage solution that saves you time and hassle, the mobile server rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability while free standing.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Suitable for rack-mount equipment where security at the rack level is not required

- Durable storage for rack-mount servers, KVM switches, and networking equipment
- Rack-mounting A/V equipment in a radio or television studio

Features

- **ADJUSTABLE DEPTH:** 15U Open frame rack with four vertical rails rack for servers & network equipment w/ adjustable mounting depth 22" to 40" (56cm to 101cm); maximize available space with 30" (77 cm) height, for integration in utility or server closet
- **EASY ASSEMBLY:** Mobile computer equipment rack with assembly instructions & easy-to-follow online video; compact flat pack shipping/packaging design to avoid damage and facilitate problem-free installations
- **COLD ROLLED STEEL:** Durable 4 Post 19" EIA/ECA-310-E open frame designed for ventilation with 15U mounting height, 1220lb (544lbs) capacity, 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling rack with cage nuts & screws to mount equipment, easy to read Units (U) & depth adjustment markings, cable management hooks for organization, with required assembly tools
- **STARTECH.COM ADVANTAGE:** Trusted by IT professionals for a variety of applications, this rack supports server depth equipment and can be used for servers, UPSs, patch panels, switches, and other networking or AV equipment. StarTech.com 2 Year Warranty and Free Lifetime Technical Support

Hardware

| | |
|------------------|---------------------------------------|
| Warranty | 2 Years |
| Wallmountable | No |
| Rack Type | 4-Post |
| Frame Type | Open Frame |
| U Height | 15U |
| Special Features | Adjustable Mounting Rails |
| | Base Plate with Floor-Anchoring Holes |
| | Built-in Cable Management |
| | Casters (Included) |
| | Grounding Lug(s) |
| | Leveling Feet |
| | Easy Assembly |

| | |
|-----------------------|-----------------------|
| | U-Markings |
| Mounting Rail Profile | L-Shape |
| Mounting Hole Types | Square (For Cage Nut) |
| Industry Standards | EIA/ECA-310-E |

Performance

| | |
|------------------------------|--------------------|
| Weight Capacity (Stationary) | 1202.2 lb [544 kg] |
|------------------------------|--------------------|

Physical Characteristics

| | |
|-----------------------------|-------------------|
| Color | Black |
| Construction Material | Steel |
| Product Length | 3.7 ft [1.1 m] |
| Product Width | 23.6 in [60.0 cm] |
| Product Height | 30.3 in [77.1 cm] |
| Weight of Product | 60.6 lb [27.4 kg] |
| Maximum Mounting Depth | 3.4 ft [1.0 m] |
| Minimum Mounting Depth | 22.3 in [56.6 cm] |
| Product Height with Casters | 33.2 in [84.4 cm] |

Packaging Information

| | |
|-------------------------------|-------------------|
| Flat Pack (Assembly Required) | Yes |
| Package Length | 36.8 in [93.5 cm] |
| Package Width | 10.8 in [27.5 cm] |
| Package Height | 5.9 in [15.0 cm] |
| Shipping (Package) Weight | 61.0 lb [27.6 kg] |

What's in the Box

| | |
|---------------------|--------|
| Included in Package | Caster |
|---------------------|--------|

M6 Flange Nut
M6 Flat Washer
M6 Hex Screw
Cable Management Hook
Hook Mounting Screw
Left Vertical Rail
Right Vertical Rail
Corner Section
Center Section
Top Bracket
M8 Flat Washer
M8 Hex Screw
10mm Wrench
13mm Wrench
Philips Head Screwdriver
Philips Head Screw
Locking Washer
M6 Screw
M6 Plastic Washer
M6 Cage Nut
Leveling Feet
Grounding Wire
Manual

****Product appearance and specifications are subject to change without notice.***

