

## 25U Adjustable Depth Open Frame 4 Post Server Rack w/ Casters / Levelers and Cable Management Hooks

Product ID: 4POSTRACK25U



The 4POSTRACK25U 25U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 25U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

## Features

- 25U Open frame design
- Adjustable mounting depth from 22 - 40in
- Supports a static loading capacity of 1200lbs (544kg)
- Easy-to-read rack Unit (U) and depth adjustment markings
- Casters, leveling feet and cable management hooks included
- Pre-drilled holes to secure the rack directly to the floor
- Easy to assemble
- Flat-packed for easy shipping

<b>Hardware</b>	Warranty	2 Years
	Wallmountable	No
	Rack Type	4-Post
	Frame Type	Open Frame
	U Height	25U
	Special Features	Adjustable Mounting Rails
	Special Features	Base Plate with Floor-Anchoring Holes
	Special Features	Built-in Cable Management
	Special Features	Grounding Lug(s)
	Special Features	Leveling Feet
	Special Features	U-Markings
	Special Features	Easy Assembly
	Special Features	Casters (Included)
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
<b>Performance</b>	Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Product Length	3.4 ft [1.0 m]
	Product Width	23.8 in [6.0 cm]
	Product Height	4.0 ft [1.2 m]

Weight of Product	72.9 lb [33.0 kg]
Maximum Mounting Depth	3.3 ft [1.0 m]
Minimum Mounting Depth	22.0 in [5.6 cm]
Product Height with Casters	4.2 ft [1.3 m]

---

<b>Packaging Information</b>	Flat Pack (Assembly Required)	Yes
	Package Length	5.0 ft [1.5 m]
	Package Width	6.3 in [1.6 cm]
	Package Height	7.9 in [2.0 cm]
	Shipping (Package) Weight	77.4 lb [35.0 kg]

---

<b>What's in the Box</b>	Included in Package	Left Vertical Rail
	Included in Package	Right Vertical Rail
	Included in Package	Base Bracket
	Included in Package	Corner Section
	Included in Package	Center Section
	Included in Package	Top Bracket
	Included in Package	M8 Bolt
	Included in Package	M8 Washer
	Included in Package	M8 (13mm) Wrench
	Included in Package	M6 (10mm) Wrench
	Included in Package	Phillips Screwdriver
	Included in Package	M6 Cage Nut
	Included in Package	PVC Cup Washer
	Included in Package	M6 Phillips Head Screw
	Included in Package	Cable Management Hook
	Included in Package	Hook Mounting Screw
	Included in Package	Casters
Included in Package	Leveling Feet	
Included in Package	M6 Screw	



Included in Package	M6 Flat Washer
Included in Package	M6 Flange Nut
Included in Package	Grounding Wires

---

***\*Product appearance and specifications are subject to change without notice.***

