

36U Adjustable 4 Post Server Equipment Open Frame Rack Cabinet

Product ID: 4POSTRACK36



The 4POSTRACK36 Adjustable Depth 36U 4-Post Rack provides a durable, open frame housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The equipment cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 36U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For added versatility, StarTech.com offers an optional 4pc Caster Kit (4POSTCASTER) that can be installed on the bottom of the 36U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

StarTech.com also offers the following Open Frame 4-Post Rack/Cabinets:

- 12U Open 4 Post Rack/Cabinet
- 25U Open 4 Post Rack/Cabinet
- 42U Open 4 Post Rack/Cabinet

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rack mount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Adjustable depth mounting rails ensure broad equipment compatibility
- Heavy-duty, pre-drilled base lets you bolt the server rack to the floor when mounting heavy rackmount equipment
- Heavy gauge mounting rails
- Unobstructed ventilation
- Optional caster kit available
- TAA compliant for GSA Schedule purchases

Hardware

| | |
|-----------------------|---|
| Warranty | Lifetime |
| Wallmountable | No |
| Rack Type | 4-Post |
| Frame Type | Open Frame |
| U Height | 36U |
| Special Features | Adjustable Mounting Rails Base Plate with Floor-Anchoring Holes Easy Assembly Casters (Optional) |
| Mounting Rail Profile | C-Shape |
| Mounting Hole Types | Square (For Cage Nut) |
| Industry Standards | EIA/ECA-310-E |

Performance

| | |
|-----------------|----------------------|
| Weight Capacity | 1000.0 lb [452.5 kg] |
|-----------------|----------------------|

Physical Characteristics

| | |
|-----------------------|-------|
| Color | Black |
| Construction Material | Steel |

Product Measurements

| | |
|-----------------------------|-------------------|
| Product Length | 23.7 in [60.1 cm] |
| Product Width | 22.6 in [57.3 cm] |
| Product Height | 5.6 ft [1.7 m] |
| Weight of Product | 96.2 lb [43.5 kg] |
| Maximum Mounting Depth | 39.4 in [100 cm] |
| Minimum Mounting Depth | 18.3 in [46.6 cm] |
| Product Height with Casters | 5.9 ft [1.8 m] |

Packaging Information

| | |
|-------------------------------|--------------------|
| Flat Pack (Assembly Required) | Yes |
| Package Length | 5.9 ft [1.8 m] |
| Package Width | 25.3 in [64.2 cm] |
| Package Height | 6.7 in [16.9 cm] |
| Shipping (Package) Weight | 104.3 lb [47.2 kg] |

What's in the Box

| | |
|---------------------|------------------------------------|
| Included in Package | 36 U Open Rack |
| | Assembly Instructions |
| | Assembly Kit (Screw, wrench, caps) |
| | M5 Screws |



M5 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

