

42U Adjustable Depth Open Frame 4 Post Server Rack Cabinet - Flat Pack w/ Casters, Levelers and Cable Management Hooks

Product ID: 4POSTRACK42



StarTech.com

The 4POSTRACK42 42U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 42U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1320lbs (600kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete rack solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securing the rack to the floor if needed, providing you with many options to customize the rack to fit your environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Flat-packed for easy shipping
- Pre-drilled holes to secure the rack directly to the floor
- Adjustable mounting depth from 22 - 40in
- Casters, leveling feet and cable management hooks included
- Easy to assemble
- Easy-to-read rack Unit (U) and depth adjustment markings
- 42U Open frame design
- Supports a static loading capacity of 1320lbs (600kg)

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	42U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Grounding Lug(s)
	Leveling Feet
	U-Markings
	Easy Assembly
	Casters (Included)
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	1326.0 lb [600 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	3.4 ft [1.0 m]
Product Width	23.8 in [60.4 cm]
Product Height	6.5 ft [2.0 m]
Weight of Product	85.1 lb [38.5 kg]
Maximum Mounting Depth	3.3 ft [1.0 m]
Minimum Mounting Depth	22.0 in [56 cm]
Product Height with Casters	6.7 ft [2.0 m]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	6.7 ft [2.0 m]
Package Width	10.6 in [27.0 cm]
Package Height	6.7 in [17.0 cm]
Shipping (Package) Weight	90.6 lb [41.0 kg]

What's in the Box

Included in Package	Left Vertical Rail
	M8 Bolt



M8 Washer
M8 (13mm) Wrench
M6 Cage Nut
PVC Cup Washer
M6 Phillips Head Screw
Cable Management Hook
Hook Mounting Screw
Casters
Leveling Feet
M6 Screw
M6 Flat Washer
M6 Flange Nut
Right Vertical Rail
Base Bracket
Center Section
Corner Section
Top Bracket
M6 (10mm) Wrench
Phillips Screwdriver
Grounding Wires
M6 grounding wire bolts (short)
M6 grounding wire lock washers

****Product appearance and specifications are subject to change without notice.***

